



		Zulässiges Drehmoment [Nm]				
		■ Permitted torque [Nm]				
		■ Couple admissible [Nm]				
Hub		50	100	150	200	250
■ Stroke						
■ Course						
$M_{x_{max}}$		350	440	520	610	700
$M_{y_{max}}$		115	143	171	200	228

			Kräfte [N]	
			■ Forces [N]	
			■ Forces [N]	
Ø 32 mm	19700	14776		
Ø 40 mm	30784	23088		
Ø 50 mm	48100	36075		