

通用配件

输送线用支脚水滴型 / 平顶固定型万向脚轮


■输送线用支脚水滴型



材质		颜色	
螺杆	底盘	螺杆	底盘
碳钢	碳钢	镀锌	—

● 适用于各种输送线设备。

自制 库存



代号	D	M	L	D ₁	B	F	F ₁	E	最大静载 P (kg)
ELE-100-M8-50-C	100	M8	50	52	13	8	10	14	150
ELE-100-M8-75-C			75						
ELE-100-M8-100-C			100						
ELE-100-M12-50-C	100	M12	50	52	13	8	10	19	200
ELE-100-M12-75-C			75						
ELE-100-M12-100-C			100						
ELE-100-M12-125-C			125						
ELE-100-M12-150-C	100	M16	150	52	13	10	13	24	300
ELE-100-M16-50-C			50						
ELE-100-M16-75-C			75						
ELE-100-M16-100-C	100	M16	100	52	13	10	13	24	300
ELE-100-M16-125-C			125						
ELE-100-M16-150-C			150						
ELE-115-M12-50-C	115	M12	50	69	14	8	10	19	200
ELE-115-M12-75-C			75						
ELE-115-M12-100-C			100						
ELE-115-M12-125-C			125						
ELE-115-M12-150-C	115	M16	150	69	14	10	13	24	300
ELE-115-M16-50-C			50						
ELE-115-M16-75-C			75						
ELE-115-M16-100-C	115	M16	100	69	14	10	13	24	300
ELE-115-M16-125-C			125						
ELE-115-M16-150-C			150						

09 通用配件




■平顶固定型万向脚轮




材质			颜色		
本体	底板	轮部	本体	底板	轮部
铸铝	Q235A	ABS	喷塑	—	—

● 具备移动和固定功能的一体式脚轮。

库存



ERE-50P-M



ERE-63P-H

代号	载重级别	D	负载 (kg)
ERE-50P-M	中系列	50	250
ERE-63P-H	重系列	63	500