

可折双幅条手轮





■ 手柄可折型·尼龙


最大降幅
20%



①代号	类型	安装方式	联轴部分		握柄安装部		握柄	
			M材质	S表面处理	M材质	颜色	M材质	颜色
HWNNJA	手柄可折型	键槽孔型	S45C		PA6		S45C	PF



HWNNJA



视角标准：第一视角



①代号 - ②D
HWNNJA - D100

型号		D ₁	D ₂	d	L	L ₁	L ₂	E	W	参考重量 (kg/pcs)
①代号	②D									
HWNNJA	100	12	25	50	38	21	18	13.8	4	0.16
	125	12	30	63	43	22	18	13.8	4	0.26
	160	16	41	80	51	25	26.5	18.3	5	0.37
	200	18	51	100	62	28	35	20.8	6	0.49



数量分类	小单	中大单	大单
数量	1-50	51-100	100~
交货期	通常	7工作日	现询





数量	1-9	10~
价格	100%	现询

G1 手柄手轮拉手
合页/门组件


■ 手柄可折型·塑胶



①代号	类型	安装方式	联轴部分		手轮主体		握柄	
			M材质	S表面处理	M材质	颜色	M材质	颜色
HWNNYA	手柄可折型	圆孔型	S45C	发黑	PA6	黑色	PA6	黑色



HWNNYA



视角标准：第一视角



①代号 - ②D
HWNNYA - D80

型号		L	L ₁	H	H ₁	参考重量 (kg/pcs)
①代号	②D					
HWNNYA	80	18	8	19	17	0.1
	100		10		17	0.16
	125	22	12	25	22	0.23
	160	26	14	29	27	0.39
	200	30	16	36	34	0.63
	250	35	20	40	38	0.93



数量分类	小单	中大单	大单
数量	1-50	51-100	100~
交货期	通常	7工作日	现询



数量	1-9	10~
价格	100%	现询

