



①代号	类型	套筒④材质
ZMSX	内螺纹式	钢制镀锌
ZMSS		不锈钢304
ZMA		铝合金

▲特点:适用于中、重负载输送,有内螺纹方便安装

视角标准:第一视角



①代号 - ②D - ③t - ④d - ⑤L
ZMSX - D38 - t1.2 - d12 - L500

型号		③t	④d	⑤L	L ₁	L ₂
ZMSX ZMSS ZMA	②D					
	■38	1.2	12	200~1800	L+9	L+10
	▲38.2	1.5	12			
	▲■50	1.5	12 15		L+8	L+9
	■50	2	12			
	▲■60	2	12 15		L+10	L+11
	■60	3	15			
	▲■76	3	15 20	200~1900	L+9	L+10
	■76	4	20			
	■80	3	20			
	▲80	4	20		L+10	L+11
	■89	3	20			
	■89	4	20			

- ▲ 尺寸为直径D=80,壁厚t=4和直径D=38.2,壁厚t=1.5只有铝合金材质
- ▲ 铝合金仅有标注▲的尺寸
- ▲ 不锈钢仅有标注■的尺寸
- ▲ 使用温度: -20°C ~80°C

④d	M	螺纹深度
12	8	15
15	10	20
20	12	25