

# 内六角螺钉

## 内六角平头带垫螺栓 / 内六角沉头螺钉




### ■内六角平头带垫螺栓



①代号	类型	[M] 材质	[S] 表面处理	强度等级
SWLAH	内六角平头带垫螺栓	碳钢	发黑	12.9
SWLBH		SUS304	-	A2-70

产品特点: 平头带垫加大了螺栓与物品的接触面积, 很好的紧固物体, 垫圈也能保护物体的表面不会受损伤。

△适用于标准: ISO7380-2-2011



#### 订购编号示例

①代号	-	② M	-	③ L
SWLAH	-	M5	-	L12


①代号	② M	③ L										P 螺距	H	D	S	
SWLAH SWLBH	3	6	8	10	12	-	16	20	25			0.5	1.65	7	2	
	4	6	8	10	12	-	16	20	25	30		0.7	2.2	9.2	2.5	
	5	6	8	10	12	-	16	20	25	30		0.8	2.75	11.4	3	
	6	6	8	10	12	14	16	20	25	30	40		1.0	3.5	13.6	4
	8	6	8	10	12	-	16	20	25	30	40		1.25	4.4	17.8	5.14

### ■内六角沉头螺钉



①代号	类型	[M] 材质	[H] 硬度	[S] 表面处理	强度等级
SWLAC	内六角沉头螺钉	SCM435	32-39HRC	发黑	10.9
SWLBC		SUS304	-	-	A2-50
SWLDC		一般结构钢	-	镀锌	8.8

△适用于标准: GB/T 70.3-2000



#### 订购编号示例

①代号	-	② M	-	③ L
SWLAC	-	M5	-	L10

型号		③ L										V	P 螺距	D (mix)	D (max)	K (max)	S					
①代号	② M	2	3	4	5	6	8	10	12	14	16	20										
(碳钢) SWLAC SWLDC	2												全牙	0.4	3.7	4	1.3	1.3				
	3		6	8	10	12	16	20	25	30	35	40	45	50	0.5	5.7	6	1.7	2			
	4		6	8	10	12	16	20	25	30	35	40	45	50	0.7	7.64	8	2.3	2.5			
	5		6	8	10	12	14	16	20	25	30	35	40	45	0.8	9.64	10	2.8	3			
	6		6	8	10	12	16	20	25	30	35	40	45	50	55	60	1	11.57	12	3.3	4	
	8			10	12	16	20	25	30	35	40	45	50	55	60	65	70	75	80	85	90	100
	10				16	20	25	30	35	40	45	50	55	60	65	70	75	80	90	100		
	12				20	25	30	35	40	45	50	55	60	65	70	75	80	90	100			
	16					30	35	40	45	50	55	60	65	70	75	80	90	100				
	20						40	45	50	55	60	65	70	75	80	90	100					

型号		③ L										V	P 螺距	D (mix)	D (max)	K (max)	S							
①代号	② M	2	2.5	3	4	5	6	8	10	12	14	16	20	25	30	35	40	45	50	55	60	65	70	
(不锈钢) SWLBC	2		5	6	8	10	12	16					全牙	0.4	3.7	4	1.3	1.32						
	2.5		5	6	8	10								0.45	4.7	5	1.5	1.5						
	3		6	8	10	12	16	20	25	30	35			0.5	5.7	6	1.7	2						
	4		6	8	10	12	16	18	20	25	30	35		0.7	7.64	8	2.3	2.5						
	5		8	10	12	14	16	20	25	30	35	40		0.8	9.64	10	2.8	3						
	6		8	10	12	14	16	20	25	30	35	40	45		1	11.57	12	3.3	4					
	8			10	12	16	20	25	30	35	40	45	50	60	1.25	15.57	16	4.4	5					
	10				16	20	25	30	35	40	45	50	55	60	65	70	1.5	19.48	20	5.5	6			