


按图定制

①代号	边长	④材质	⑤表面处理	最高使用压力
MALAEKP	30×40	铝合金	-	1MPa(≈10.2Kg/cm ²)以下



视角标准：第一视角



①代号 - ②侧面孔数K - ③螺纹代号L
MALAEKP - K2 - L11

①代号	②侧面孔数K	③螺纹代号L	d1 Rc(PT)	d2 Rc(PT)
	K	L		
MALAEKP (30×40)	1	11	1/8	1/8
		22	1/4	1/4
	2	11	1/8	1/8
		12	1/8	1/4
	3	11	1/8	1/8
		22	1/4	1/4
	4	11	1/8	1/8
		12	1/8	1/4
	5	12	1/8	1/4
		22	1/4	1/4
	6	12	1/8	1/4
		22	1/4	1/4

▲ 螺纹代号：如12，表示d₁为1/8管螺纹，d₂为1/4管螺纹。

L5
歧管块



爱安特自营商城焕新登场，注册有礼，一键直达



400-6699-428



www.ant-fa.com