



## Raccordo NPT maschio 45° in ottone nichelato



Filetto NPT	Sealtite Ø (inch)	Passaggio utile (mm)	Dimensioni in mm					Confezione standard	Codice articolo	Peso (Kg/100)
			A	B	C	D	E			
1/2" NPT	5/16"	8,3	23	12	26	33	22	50	814.411.1*	7,9
1/2" NPT	3/8"	10,2	23	12	26	33	22	50	814.412.1	7,9
1/2" NPT	1/2"	13,9	25	13	29	33	27	50	814.416.1	10,7
3/4" NPT	3/4"	18,5	30	15	35	36	33	25	814.420.1	15,7
1" NPT	1"	23,8	34	15	45	46	42	10	814.426.1	31,8
1.1/4" NPT	1.1/4"	31,8	39	16	54	54	51	5	814.435.1	54,2
1.1/2" NPT	1.1/2"	36,8	45	18	63	59	60	5	814.440.1	78,5
2" NPT	2"	47,8	53	20	77	71	74	4	814.450.1	132,0

\* Raccordi per guaine con diametro 5/16" sono privi di omologazione UL/CSA.


## Raccordo NPT maschio 90° in ottone nichelato



Filetto NPT	Sealtite Ø (inch)	Passaggio utile (mm)	Dimensioni in mm					Confezione standard	Codice articolo	Peso (Kg/100)
			A	B	C	D	E			
1/2" NPT	5/16"	8,3	32	12	26	42	22	50	814.911.1*	13,3
1/2" NPT	3/8"	10,2	32	12	26	42	22	50	814.912.1	13,3
1/2" NPT	1/2"	13,9	36	13	29	43	27	50	814.916.1	14,6
3/4" NPT	3/4"	18,5	43	15	35	48	33	25	814.920.1	22,0
1" NPT	1"	23,8	48	15	45	59	42	10	814.926.1	31,7
1.1/4" NPT	1.1/4"	31,8	57	16	54	68	51	5	814.935.1	62,5
1.1/2" NPT	1.1/2"	36,8	63	18	63	78	60	5	814.940.1	89,1
2" NPT	2"	47,8	74	20	77	96	74	4	814.950.1	141,9

\* Raccordi per guaine con diametro 5/16" sono privi di omologazione UL/CSA.

## Raccordo-pressacavo NPT in ottone nichelato



Filetto NPT	Sealtite Ø (inch)	Ø cavo min-max (mm)	Dimensioni in mm					Confezione standard	Codice articolo	Peso (Kg/100)
			A	B	C	E	F			
3/8" NPT	5/16"	4 - 8	60	15	26	24	17	25	814.709.1	7,8
3/8" NPT	3/8"	4 - 8	60	15	26	24	17	25	814.710.1	7,8
1/2" NPT	3/8"	6 - 10,2	57	13	26	24	22	25	814.712.1	11,7
1/2" NPT	1/2"	6 - 12	59	13	29	27	22	25	814.715.1	11,7
3/4" NPT	3/4"	13 - 18	68	13	35	33	30	25	814.721.1	19,6

## Viola tornita in ottone nichelato



Filetto	Sealtite Ø (inch)	Passaggio utile (mm)	Dimensioni in mm					Confezione standard	Codice articolo	Peso (Kg/100)
			A	B	C	D	E			
-	1/4"	5,2	-	-	-	-	-	25	815.006.0	-
-	5/16"	8,3	-	-	-	-	-	25	815.010.0	-
-	3/8"	10,2	-	-	-	-	-	25	815.011.4	-
-	1/2"	13,9	-	-	-	-	-	25	815.016.4	-
-	3/4"	18,5	-	-	-	-	-	25	815.021.4	-
-	1"	23,8	-	-	-	-	-	5	815.029.4	-
-	1.1/4"	31,8	-	-	-	-	-	5	815.036.0	-
-	1.1/2"	36,8	-	-	-	-	-	5	815.042.0	-
-	2"	47,8	-	-	-	-	-	2	815.048.0	-

RACCORDI  
ANACONDA

RACCORDI  
A TENUTA  
STAGNA IP 67  
PER SEALTITE