



**ISO straight swivel fitting, male, nickel plated brass
(including connection set).**




Thread	UIG/UI Size (inch)	Min. Internal Bore (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	D	E			
M16 x 1,5	3/8"	9,8	48	10	26	24	21	10	813.016.7	10,1
M20 x 1,5	1/2"	13,9	49	10	29	27	25	10	813.020.7	12,6
M25 x 1,5	3/4"	17,4	49	10	35	33	31	5	813.025.7	17,6
M32 x 1,5	1"	22,8	55	12	45	42	38	5	813.032.7	36,5
M40 x 1,5	1.1/4"	29,4	58	14	54	50	48	2	813.040.7	66,6
M50 x 1,5	1.1/2"	36,9	65	14	62	58	55	2	813.050.7	74,0
M63 x 1,5	2"	47,9	74	16	76	72	68	2	813.063.7	130,0

**Pg straight compact fitting, male, nickel plated brass
(including connection set).**



Thread	UIG/UI Size (inch)	Min. Internal Bore (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	D	E			
Pg 11	3/8"	9,8	30	10	26	-	24	10	710.011.7	4,8
Pg 13,5	3/8"	9,8	30	10	26	-	24	10	710.013.7	4,6
Pg 16	1/2"	13,9	32	10	29	-	27	10	710.016.7	5,3
Pg 21	3/4"	18,5	33	10	35	-	33	5	710.021.7	7,8
Pg 29	1"	22,8	36	12	45	-	44	5	710.029.7	14,4
Pg 36	1.1/4"	30,8	40	13	53	-	52	2	710.036.7	19,1
Pg 42	1.1/2"	36,9	46	14	62	-	60	2	710.042.7	29,4
Pg 48	2"	47,9	52	16	76	-	72	2	710.048.7	43,4

**NPT straight compact fitting, male, nickel plated brass
(including connection set).**



Thread	UIG/UI Size (inch)	Min. Internal Bore (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	D	E			
NPT 1/2"	3/8"	9,8	32	12	26	-	24	10	714.012.7	4,8
NPT 1/2"	1/2"	13,9	34	12	29	-	27	10	714.016.7	5,7
NPT 3/4"	3/4"	18,5	35	12	35	-	33	5	714.020.7	8,2
NPT 1"	1"	22,8	37	13	45	-	44	5	714.026.7	14,7
NPT 1.1/4"	1.1/4"	30,8	42	15	53	-	52	2	714.035.7	22,4
NPT 1.1/2"	1.1/2"	36,9	48	16	62	-	60	2	714.040.7	29,7
NPT 2"	2"	47,9	54	19	76	-	72	2	714.050.7	47,8

Conduit connector, nickel plated brass.



Thread	UIG/UI Size (inch)	Min. Internal Bore (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	D	E			
-	3/8"	9,8	-	-	-	-	-	10	784.012.7	11,4
-	1/2"	13,9	-	-	-	-	-	10	784.016.7	13,8
-	3/4"	18,5	-	-	-	-	-	5	784.020.7	20,6
-	1"	22,8	-	-	-	-	-	5	784.026.7	33,2
-	1.1/4"	30,8	-	-	-	-	-	2	784.035.7	52,2
-	1.1/2"	36,9	-	-	-	-	-	2	784.040.7	-
-	2"	47,9	-	-	-	-	-	2	784.050.7	-

**ANACONDA
MULTIFLEX**

**FITTINGS FOR
TYPE UIG / UI
IP 40**