

<b>PARA-FLEX COUPLINGS NOMENCLATURE</b>			
<b>VARIABLE DESCRIPTION</b>	<b>NAME OF A VARIABLE</b>	<b>EXA MPL E</b>	<b>DESCRIPTION</b>
<b>O.D. OF COUPLING</b>	<b>SIZE (INCH)</b>	<b>3-1/4</b>	<b>OPTIONS: 2-5/8, 3-1/4, 4, 5-1/4, 7, 8, 10.</b>
<b>BORE</b>	<b>BORE (INCH)</b>	<b>1-9/16</b>	<b>OPTIONS: DIFFERENT FOR EACH SIZE.</b>
<b>TLFO</b>	<b>TAPER-LOCK FLANGE OPTIONS</b>	<b>TL</b>	<b>OPTIONS: TYPE H-F, TYPE H-H, TYPE F-F.</b>

**ASSEMBLY PART NUMBER EXAMPLES:**

**3-1/4-HH-3/4 – DESCRIPTION: 3-1/4” OUTSIDE DIAMETER OF A COUPLING, H-H TYPE TAPER-LOCK FLANGE, 3/4” BORE.**

**7-HF-1-1/16 – DESCRIPTION: 7” OUTSIDE DIAMETER OF A COUPLING, H-F TYPE TAPER- LOCK FLANGE, 1-1/16” BORE.**

**10-FF-2-5/8 – DESCRIPTION: 10” OUTSIDE DIAMETER OF A COUPLING, F-F TYPE TAPER- LOCK FLANGE, 2-5/8” BORE.**