


## Dimensions (bore size: $\phi 12$ )



### ● LCG-12

Stroke length: 10, 20, 30, 40, 50

(The main body fixing holes in this drawing is for 30 mm stroke)



### Dimensions table per stroke length


Stroke length	10	20	30	40	50
L1		91		101	111
L2		79		89	99
n		2		3	
V		66.5		76.5	86.5
W		26		36	46
X		37.5		36	32
Y		32.5		31	57
RD	41.5	31.5		21.5	
HD		27			

### Dimensions (bore size: $\phi 12$ )

● LCG-12

Stroke length: 75,100

(The main body fixing holes in this drawing is for 100 mm stroke)



Dimensions table per stroke length

Stroke length	75	100
L1	145	170
L2	133	158
V	116	141
W	55	80
X	34.5	47
Y	89.5	102
RD	21.5	
HD	36	

SCP*2
CMK2
CMA2
SCM
SCG
SCA2
SCS
CKV2
CA/OV2
SSD
CAT
MDC2
MVC
SMD2
MSD*
FC*
STK
ULK*
JSK/M2
JSG
JSC3
USSD
USC
JSB3
LMB
STG
STS/L
LCS
<b>LCG</b>
LCM
LCT
LCY
STR2
UCA2
HCM
HCA
SRL2
SRG
SRM
SRT
MRL2
MRG2
SM-25
CAC3
UCAC
RCC2
MFC
SHC
GLC
Ending

Linear slide cylinder  
Combined functions