

## Front/rear Plinths, PF

- Description:** Front and rear plinth sections. For cabling without any restrictions and in accordance with the VDE 0113 standard. The plinth consists of four corner pieces with removable front covers. The side panels PS are to be ordered separately. Produced in 100 mm and 200 mm heights. 200 mm high plinths are delivered with a rear cover for cabling that consists of two removable panels 100 mm high. The front cover is a one piece panel of 200 mm high. All panels have double returns on each side for added strength.
- Material:** Corner pieces in 2 mm and panels in 1.5 mm mild steel.
- Finish:** RAL 7022 structured powder coating.
- Pack quantity:** 1 set of 4 corner pieces including covers. Front and rear panel (2 rear panels for 200 mm high plinths) with mounting accessories. Mounting accessories for side panels PST.
- Mounting requirement:** Add the side panels PS for a complete plinth. When combining enclosures it is recommended to add transversal panels PCP for cable duct support and extra rigidity.



| For console |      |          |
|-------------|------|----------|
| H           | W    | Item no. |
| 100         | 400  | PF1040   |
| 100         | 500  | PF1050   |
| 100         | 600  | PF1060   |
| 100         | 800  | PF1080   |
| 100         | 1000 | PF1100   |
| 100         | 1200 | PF1120   |
| 200         | 400  | PF2040   |
| 200         | 500  | PF2050   |
| 200         | 600  | PF2060   |
| 200         | 800  | PF2080   |
| 200         | 1000 | PF2100   |
| 200         | 1200 | PF2120   |

For console 1600 mm wide use 2 x 800 mm wide plinth.

## Plinth Side panels, PST

- Description:** Mounted directly to the corner pieces.
- Material:** 1.5 mm mild steel.
- Finish:** RAL 7022 structured powder coating.
- Pack quantity:** 2 side panels, mounting accessories included in PF package.

| For console |     |          |
|-------------|-----|----------|
| H           | D   | Item no. |
| 100         | 400 | PST1040  |
| 100         | 500 | PST1050  |
| 200         | 400 | PST2040  |
| 200         | 500 | PST2050  |

