

# Thermal Management

## Control Range

### Accessories

## Thermostat, ETR200

<b>Description:</b>	Thermostat with changeover contact to manage any kind of device, heater or cooling. Sensor element thermostatic bimetal. Mounting clip for 35 mm DIN rail (EN 60715).
<b>Material:</b>	Plastic according to UL94 V-0.
<b>Setting range:</b>	0°C to 60°C. Switching temperature difference less than 3°K, and switching point tolerance $\pm 3^{\circ}\text{K}$ .
<b>Switch capacity:</b>	NC contact, 100-250V AC, 10(2)A. NO contact, 100-250V AC, 5(2)A, for 230V AC operation only. 24V DC, 30W. Value in brackets for inductive load.
<b>Operating temperature:</b>	-40 to +80°C.
<b>Service life:</b>	> 100,000 cycles.
<b>Connection:</b>	Screw terminal for cable (0.5 to 2.5 mm <sup>2</sup> ).
<b>Protection:</b>	IP 20.
<b>Approvals:</b>	CE, EAC, cULus_UL Listed.
<b>Finish:</b>	RAL 7035.
<b>Pack quantity:</b>	1 piece.



Item no.
ETR200

