



Description: Window kits are ideal for visibility of internal enclosure components. Secure sealing with silicone gasket to protect against water and dust ingress in extreme temperature applications.

Material: Frame: Type 316 stainless steel. Gasket: Silicone.
Window: Tempered safety glass, 6 mm.

Heating element: Leak compensation:Continuous flow:Switch capacity:Gasket:Operating temperature: -55 (-67) to 180 °C (356 °F).

Connection: Type of connection:Flammability:Body:Cover:Door:Lock:Mounting plate:Cable access:Protection:IP 66 | TYPE 4, 4X, 12, 3R

Finish: Approvals:ATEX Directive 94/9/EC; Sira 13ATEX3315U; Ex e IIC Gb; Ex tb IIIC Db IP 66; IECEx; IECEx SIR 13.0123U; Ex e IIC Gb; Ex tb IIIC Db IP 66; UL 508A Component Recognized; Type 4, 4X,12, 3R; File No. E61997.

Delivery: Scope of delivery:Requirements:Mounting:Pack quantity:1 piece with mounting accessories.

Note:

H	W	D	Viewing area height	Viewing area width	Cutout Size HxW	Item no.
191	140	36	127	76	170 x 119	EXWK53SS6
292	203	36	229	140	272 x 183	EXWK95SS6
241	343	36	178	279	211 x 392	EXWK711SS6
394	267	36	330	203	373 x 246	EXWK138SS6
241	445	36	178	381	211 x 424	EXWK715SS6
495	343	36	432	279	475 x 322	EXWK1711SS6
241	572	36	178	508	221 x 551	EXWK720SS6
648	445	36	584	381	627 x 424	EXWK2315SS6
241	673	36	178	610	653 x 221	EXWK724SS6
241	800	36	178	737	221 x 780	EXWK729SS6
800	546	36	737	483	780 x 526	EXWK2919SS6