

Slim Fit indoor cooling unit

Slim Fit indoor cooling unit

nVent

HOFFMAN

CONNECT AND PROTECT



Description: The Slim Fit indoor air conditioner has extensive features and options. The units have an attractive design that also help optimize the air flow. The units are delivered with a smart controller. The standard unit has three mounting options: Surface, partial recess and fully recess mount (not applicable to 300W model), that are easy to change. The air conditioners are available for a cooling range from 300 W to 4000 W. All units are equipped with active condensate management with a heater strip. The factory thermostat setting is 35 °C.

Type of connection: Terminal block.

Material: Galvanized steel powder coated. Aesthetic designed plastic cover to optimize air flow.

Temperature limits inside: +20 °C... + 55 °C

Temperature limits outside: +10 °C... + 55 °C

Protection: IP54 | TYPE 12

Finish: Powder Coat Semi-textured RAL 7035 Light Grey Standard.