


BOHRBUCHSE MIT BUND, DIN 172 FORM A



276.



Werkstoff:

Einsatzstahl
Härte 740 ± 40 HV 10

Ausführung:

Durchmesser d_1 , d_2 und Auflagefläche am Bund geschliffen.

Andere Längen und Durchmesser auf Anfrage.

276. Bohrbuchse mit Bund, DIN 172 Form A

d_1	d_2	d_3	Stufung	l_1	6	8	9	10	12	16	20	25	28	30	36	45	56	67
0,9 - 1	3	6	0.1	l_2	4		7											
1,1 - 1,8	4	7	0.1		4		7											
1,9 - 2,6	5	8	0.1		4		7											
2,7 - 3,3	6	9	0.1			5.5			9.5	13.5								
3,4 - 4	7	10	0.1			5.5			9.5	13.5								
4,1 - 5	8	11	0.1			5.5			9.5	13.5								
5,1 - 6	10	13	0.1				7			13	17							
6,1 - 8	12	15	0.1					7		13	17							
8,1 - 10	15	18	0.1						9		17	22						
10,1 - 12	18	22	0.1						8		16	21						
12,1 - 15	22	26	0.1							12			24		32			
15,5 - 18	26	30	0.5							12			24		32			
18,5 - 22	30	34	0.5								15				31	40		
22,5 - 26	35	39	0.5								15				31	40		
26,5 - 30	42	46	0.5									20				40	51	
30,5 - 35	48	52	0.5									20				40	51	
35,5 - 42	55	59	0.5											25			51	62

Bestell-Beispiel:

Bohrbuchse mit Bund, DIN 172 Form A	=	276.1.
Führungsdurchmesser d_1	12.1 mm =	1210.
Länge l_1	16 mm =	016
Bestell-Nummer	=	276.1. 1210.016