


滑板, 带烧结层的钢材, VDI 3357



2960.31.



描述:
带烧结层的钢材为双层材料。即便在持续运行时, 其也可确保低维护使用。

材料:
带烧结层的钢板,
润滑剂比重 20-25%。

说明:
不提供螺栓。

固定件:
使用符合 DIN EN ISO 4762 M12 标准的圆柱头螺栓。

2960.31. 滑板, 带烧结层的钢材, VDI 3357

订购编号	b	l ₁	l ₂	l ₃	l ₄	l ₅	d	d ₁	t	钻孔数量
2960.31.050.250	50	250	25	85	165	225	13.5	20	13	4
2960.31.050.300	50	300	25	105	195	275	13.5	20	13	4
2960.31.050.350	50	350	25	125	225	325	13.5	20	13	4
2960.31.050.400	50	400	25	145	255	375	13.5	20	13	4
2960.31.050.450	50	450	25	165	285	425	13.5	20	13	4
2960.31.050.500	50	500	25	175	325	475	13.5	20	13	4
2960.31.080.250	80	250	25	85	165	225	13.5	20	13	4
2960.31.080.300	80	300	25	105	195	275	13.5	20	13	4
2960.31.080.350	80	350	25	125	225	325	13.5	20	13	4
2960.31.080.400	80	400	25	145	255	375	13.5	20	13	4
2960.31.080.450	80	450	25	165	285	425	13.5	20	13	4
2960.31.080.500	80	500	25	175	325	475	13.5	20	13	4
2960.31.100.250	100	250	25	85	165	225	13.5	20	13	4
2960.31.100.300	100	300	25	105	195	275	13.5	20	13	4
2960.31.100.350	100	350	25	125	225	325	13.5	20	13	4
2960.31.100.400	100	400	25	145	255	375	13.5	20	13	4
2960.31.100.450	100	450	25	165	285	425	13.5	20	13	4
2960.31.100.500	100	500	25	175	325	475	13.5	20	13	4
2960.31.125.250	125	250	25	85	165	225	13.5	20	13	4
2960.31.125.300	125	300	25	105	195	275	13.5	20	13	4
2960.31.125.350	125	350	25	125	225	325	13.5	20	13	4
2960.31.125.400	125	400	25	145	255	375	13.5	20	13	4
2960.31.125.450	125	450	25	165	285	425	13.5	20	13	4
2960.31.125.500	125	500	25	175	325	475	13.5	20	13	4
2960.31.160.250	160	250	25	85	165	225	13.5	20	13	4
2960.31.160.300	160	300	25	105	195	275	13.5	20	13	4
2960.31.160.350	160	350	25	125	225	325	13.5	20	13	4
2960.31.160.400	160	400	25	145	255	375	13.5	20	13	4
2960.31.160.450	160	450	25	165	285	425	13.5	20	13	4
2960.31.160.500	160	500	25	175	325	475	13.5	20	13	4