




材料:
钢, 表面硬化处理。


说明:
不提供螺栓。

固定件:
使用符合 DIN EN ISO 4762 M10 标准的圆柱头螺栓。

2960.44.45.



2960.44.45.



滑板, 钢 带油槽, CNOMO

2960.44.45. 滑板, 钢 带油槽, CNOMO

订购编号	形状	b	a	e	e ₁	e ₂	e ₃	e ₄	e ₅	e ₆	e ₇	e ₈	e ₉	螺栓孔数量
2960.44.45.070.100	A	70	100		20	-	-	70	-	-	-	-	10	2
2960.44.45.070.150	B	70	150		10	20	-	70	120	-	-	-	10	3
2960.44.45.070.200	D	70	200		20	-	-	70	120	170	-	-	10	4
2960.44.45.100.100	I	100	100		30	50	-	45	70	-	-	-	25	3
2960.44.45.100.150	C	100	150		50	-	-	45	95	120	-	-	25	4
2960.44.45.100.200	D	100	200		50	-	-	70	120	170	-	-	25	4
2960.44.45.100.250	E	100	250		50	-	-	70	120	170	220	-	25	5
2960.44.45.100.300	F	100	300		50	-	-	70	120	170	220	270	25	6
2960.44.45.150.100	G	150	100		25	75	100	70	-	-	-	-	50	4
2960.44.45.150.150	H	150	150		25	75	100	45	95	120	-	-	50	4
2960.44.45.150.200	D	150	200		100	-	-	70	120	170	-	-	50	4
2960.44.45.150.250	E	150	250		100	-	-	70	120	170	220	-	50	5
2960.44.45.150.300	F	150	300		100	-	-	70	120	170	220	270	50	6
2960.44.45.200.100	G	200	100		50	100	150	70	-	-	-	-	75	4