


SÜRTÜNME PLAKASI, BRONZ KENDİNDEN YAĞLAMALI

2961.71.



2961.71. Sürtünme Plakası, Bronz Kendinden Yağlamalı

Sipariş No.	b	s	l	305	605	1.005
2961.71.020.004.	20	4		●		
2961.71.025.005.	25	5		●		
2961.71.030.004.	30	4		●		
2961.71.030.006.	30	6		●	●	
2961.71.030.008.	30	8		●	●	
2961.71.030.010.	30	10		●	●	●
2961.71.030.012.	30	12		●	●	●
2961.71.035.010.	35	10		●	●	●
2961.71.040.005.	40	5		●	●	
2961.71.040.006.	40	6		●	●	
2961.71.040.008.	40	8		●	●	●
2961.71.040.010.	40	10		●	●	●
2961.71.040.012.	40	12		●	●	●
2961.71.040.016.	40	16		●	●	●
2961.71.050.010.	50	10		●	●	●
2961.71.050.012.	50	12		●	●	●
2961.71.050.020.	50	20		●	●	●
2961.71.060.012.	60	12		●	●	●
2961.71.060.016.	60	16		●	●	●
2961.71.080.010.	80	10		●	●	●
2961.71.080.012.	80	12		●	●	●
2961.71.080.016.	80	16		●	●	●
2961.71.080.020.	80	20		●	●	●
2961.71.080.025.	80	25		●	●	●
2961.71.100.016.	100	16		●	●	●
2961.71.100.020.	100	20		●	●	●
2961.71.100.025.	100	25		●	●	●
2961.71.125.020.	125	20		●	●	●
2961.71.125.025.	125	25		●	●	●
2961.71.160.025.	160	25		●	●	●

Malzeme:

Bronz Kendinden Yağlamalı

Yürütme:

Sürtünme yüzeyleri taşlanmış.

Siparis Kodu (örnek):

Sürtünme Plakası, Bronz Kendinden Yağlamalı	=	2961.71.
Genişlik b	50 mm	= 050.
Kalınlık s	10 mm	= 010.
Uzunluk l	1005 mm	= 1005
Siparis No	=	2961.71. 050. 010. 1005