



... mit Flansch ...

Abmessungen Dimensions [mm]

Gewinde Thread d1 x P	d2	d3	d4	d5	b1	b2	SW	Bestellnummer Part No. FR(L)M- ...
<b>Metrische Gewinde Metric thread</b>								
M3x0,5	9	18	15,2	3,2	13	3		...0913M3
M4x0,7	9	18	15,2	3,2	13	3		...0913M4
M5x0,8	9	18	15,2	3,2	13	3		...0913M5
M5x0,8	9	18	15,2	3,2	13	3	9	...090913M5
M6x1	13	25	19	3,2	15	5		...0913M6
<b>Trapezgewinde Trapezoidal thread</b>								
Tr06x2P1	13	25	19	3,2	15	5		...1315TR06X2P1
Tr06x2P1	13	25	19	3,2	15	5	13	...131315TR06X2P1
Tr08x1,5	20	36	28	4	20	8		...2020TR08X1.5
Tr08x1,5	20	36	28	4	20	8	20	...202020TR08X1.5
Tr10x2	25	42	34	5	25	10		...2525TR10X2
Tr10x2	25	42	34	5	25	10	25	...252525TR10X2
Tr10x3	25	42	34	5	25	10		...2525TR10X3
Tr12x3	28	48	38	6	35	12		...2835TR12X3
Tr12x3	28	48	38	6	35	12	28	...282835TR12X3
Tr12x6P3	28	48	38	6	35	12		...2835TR12X6P3
Tr14x3	28	48	38	6	35	12		...2835TR14X3
Tr14x4	28	48	38	6	35	12		...2835TR14X4
Tr14x4	28	48	38	6	35	12	28	...282835TR14X4
Tr16x2	28	48	38	6	35	12		...2835TR16X2

- J** Hohe Geschwindigkeiten High speed
- W300** Hoch belastbar High load capacity
- J350** Temperaturen bis zu 150 °C  
Temperatures up to 150 °C
- A180** FDA-konform FDA-compliant
- R** Günstig Low-cost

**Bestellschlüssel**  
Order key

Typ Type	Abmessungen Dimensions	Gewinde Thread
<input type="checkbox"/> F	R	M - 25 25 25

**iglicur® -Material wählen**  
Choose iglicur® material

- Form F = mit Flansch  
with flange
- R = Rechtsgewinde  
right handed thread
- Metrisch metric
- Schlüsselfweite SW  
Wide across flats
- d2
- b1
- TR= Trapezgewinde  
Trapezoidal thread
- Ø
- Steigung Pitch

**Optionen Options:**  
**R** = Rechtsgewinde Right handed thread  
**L** = Linksgewinde Left handed thread  
**TR** = Trapezgewinde Trapezoidal thread  
**M** = Metrisches Gewinde Metric thread

in 5 Materialien ...

Abmessungen Dimensions [mm]

Gewinde Thread d1 x P	d2	d3	d4	d5	b1	b2	SW	Bestellnummer Part No. FR(L)M- ...
<b>Trapezgewinde Trapezoidal thread</b>								
Tr16x4	28	48	38	6	35	12		...2835TR16X4
Tr16x4	28	48	38	6	35	12	28	...282835TR16X4
Tr16x8P4	28	48	38	6	35	12		...2835TR6X8P4
Tr18x4	28	48	38	6	35	12		...2835TR18X4
Tr18x4	28	48	38	6	35	12	28	...282835TR18X4
Tr18x8P4	28	48	38	6	35	12		...2835TR18X8P4
Tr20x4	32	55	45	7	44	12		...3244TR20X4
Tr20x8P4	32	55	45	7	44	12		...3244TR20X8P4
Tr24x5	32	55	45	7	44	12		...3244TR24X5
Tr26x5	38	62	50	7	46	14		...3846TR26X5
Tr28x5	38	62	50	7	46	14		...3846TR28X5
Tr30x6	38	62	50	7	46	14		...3846TR30X6
Tr30x6	45	70	58	7	46	16		...4546TR30X6
Tr36x6	45	70	58	7	88	16		...4588TR36X6
Tr36x6	67	95	81	7	70	25		...6770TR36X6
Tr40x7	67	95	81	7	70	25		...6770TR40X7