



* Bei Wanddicke < 1 mm: Fase = 20°
Thickness < 1 mm: Chamfer = 20°

Abmessungen nach
Dimensions according to
ISO 3547-1

Gleitlager mit Bund z.B. aus iglidur® G
Flange bearing i.e. made from iglidur® G

... und mit Bund ...

Gleitlager mit Bund Flange bearing

d1	d2	b1	d3	b2	Art.-Nr. Part No.
1/8	3/16	3/16	0.312	0.032	<input type="checkbox"/> FI-0203-03
3/16	1/4	1/4	.375	0.032	<input type="checkbox"/> FI-0304-04
1/4	5/16	3/8	.500	0.032	<input type="checkbox"/> FI-0405-06
1/4	5/16	1/2	.500	0.032	<input type="checkbox"/> FI-0405-08
5/16	3/8	1/4	0.562	0.032	<input type="checkbox"/> FI-0506-04
5/16	3/8	3/8	0.562	0.032	<input type="checkbox"/> FI-0506-06
5/16	3/8	1/2	0.562	0.032	<input type="checkbox"/> FI-0506-08
3/8	15/32	1/4	.687	.046	<input type="checkbox"/> FI-0607-04
3/8	15/32	3/8	.687	.046	<input type="checkbox"/> FI-0607-06
3/8	15/32	1/2	.687	.046	<input type="checkbox"/> FI-0607-08
3/8	15/32	3/4	.687	.046	<input type="checkbox"/> FI-0607-12
7/16	17/32	1/2	.750	.046	<input type="checkbox"/> FI-0708-08
1/2	19/32	1/4	.875	.046	<input type="checkbox"/> FI-0809-04
1/2	19/32	3/8	.875	.046	<input type="checkbox"/> FI-0809-06
1/2	19/32	1/2	.875	.046	<input type="checkbox"/> FI-0809-08
1/2	19/32	3/4	.875	.046	<input type="checkbox"/> FI-0809-12
1/2	19/32	1	0.875	.046	<input type="checkbox"/> FI-0809-16
5/8	23/32	1/2	.937	.046	<input type="checkbox"/> FI-1011-08
5/8	23/32	3/4	.937	.046	<input type="checkbox"/> FI-1011-12
5/8	23/32	1	.937	.046	<input type="checkbox"/> FI-1011-16
3/4	7/8	1/2	1.125	.062	<input type="checkbox"/> FI-1214-08
3/4	7/8	3/4	1.125	.062	<input type="checkbox"/> FI-1214-12

Wählen Sie Material und Abmessungen passend für Ihre Anwendung
Choose the suitable material and dimensions for your application

- iglidur® A181
- A350
- A500
- G
- H1
- H370
- J
- J3
- J350
- P
- P210
- Q2
- W(300)
- X
- Z

Typ Type	Abmessungen [mm] Dimensions			
<input type="checkbox"/>	FI	- 09	10	- 08
Material wählen Choose material	FI = mit Bund flange bearing	Innen-Ø Inner-Ø d1	Außen-Ø Outer-Ø d2	Länge Length b1

Bestellbeispiel Order example
H1 FI-0910-08

Flanschlager aus iglidur® H1,
Innen-Ø Inner-Ø: 9/16 Inch,
Außen-Ø Outer-Ø: 21/32 Inch,
Länge Length: 1/2 Inch

... in Inch ...

Gleitlager mit Bund Flange bearing

d1	d2	b1	d3	b2	Art.-Nr. Part No.
3/4	7/8	1	1.125	.062	<input type="checkbox"/> FI-1214-16
7/8	1	1/2	1.250	.062	<input type="checkbox"/> FI-1416-08
7/8	1	3/4	1.250	.062	<input type="checkbox"/> FI-1416-12
7/8	1	1	1.250	.062	<input type="checkbox"/> FI-1416-16
1	1 1/8	1/2	1.375	.062	<input type="checkbox"/> FI-1618-08
1	1 1/8	3/4	1.375	.062	<input type="checkbox"/> FI-1618-12
1	1 1/8	1	1.375	.062	<input type="checkbox"/> FI-1618-16
1 1/4	1 13/32	1	1.687	0.078	<input type="checkbox"/> FI-2022-16
1 1/4	1 13/32	1 1/4	1.687	.078	<input type="checkbox"/> FI-2022-20
1 1/2	1 21/32	1	2.000	.078	<input type="checkbox"/> FI-2426-16
1 1/2	1 21/32	1 1/2	2.000	.078	<input type="checkbox"/> FI-2426-24
1 3/4	1 15/16	2	2.375	.093	<input type="checkbox"/> FI-2831-32
2	2 3/16	2	2.625	.093	<input type="checkbox"/> FI-3235-32

Online berechenbar Calculate online
www.igus.de/iglidur-experte
www.igus.eu/iglidur-expert

Lieferbar Available
ab Lager from stock
(4 Wochen für Erstauslieferung)
(4 weeks for initial delivery)

Mehr Informationen More information
www.igus.de/iglidur-standards
www.igus.eu/iglidur-standards