

Cable management

Cable routing



Cable management duct

for TS

For side cable routing. The cable management duct is attached to 482.6 mm (19") mounting angles at the sides of the 800 mm wide TS network enclosure. For this purpose, the mounting angles must be mounted on installation brackets. Thanks to the removable front trim panel equipped with quick-release fasteners, cables can also be retrospectively removed or added.

Dimensions:

W x D: 95 x 94 mm

Material:

Sheet steel, spray-finished

Colour:

RAL 7035

Supply includes:

Assembly parts.

U	For enclosure height mm	Model No. DK
31	1600	7827.333
36	1800	7827.338
40	2000	7827.342
45	2200	7827.347



Also required:

Installation brackets TS for mounting angles, see page 1096.



Cable routing components

for FR (i)

For snap-fastening into the vertical frame channel.

Type 1:

With horizontal bar for attaching the cables in the frame channel.



Type 2:

Additionally with semi-circular bead for kink-free cable entry and exit.

Type	Packs of	Model No. DK
1	10	7218.100
2	10	7218.105

Material:

Polycarbonate

Colour:

RAL 7035



Extension kit

horizontal cable management

for FR(i)

Allows the enclosure frame to be extended in the depth by approximately 100 mm. The space thereby acquired may be used for horizontal cable management between bayed enclosures.

Material:

Sheet steel, zinc-plated, passivated

Supply includes:

1 set =

8 spacer supports, including assembly parts.

Extension kit

Packs of	Model No. FR
1 set	7856.740

Note:

Combination of the extension kit with divided doors is not possible.

Trim panels

Enclosure height mm	Packs of	Model No. FR
2000	2	7856.743
2200	2	7856.746

Note:

Upon request, trim panels may be inserted on the outer sides of the bayed enclosure suites to protect the enclosures against unauthorised access.

