

Baying systems TS 8

3 SV-TS 8 cable chamber enclosures (height 2000 mm)

Width mm	Packs of	300	400	600	300	400	600	Page	
Height mm		2000	2000	2000	2000	2000	2000		
Depth mm		600	600	600	800	800	800		
Model No. SV	1	9670.316	9670.416	9670.616	9670.318	9670.418	9670.618		
Door(s)		1	1	1	1	1	1		
Weight (kg)		48.5	53.8	69.4	50.4	55.9	74.0		
Base/plinth									
Components front and rear	Height 100 mm	1 set	8601.915	8601.400	8601.600	8601.915	8601.400	8601.600	543
	Height 200 mm	1 set	8602.915	8602.400	8602.600	8602.915	8602.400	8602.600	543
Trim panels, sides	Height 100 mm	1 set	8601.060	8601.060	8601.060	8601.080	8601.080	8601.080	544
	Height 200 mm	1 set	8602.060	8602.060	8602.060	8602.080	8602.080	8602.080	544
Flex-Block									see page 540
Levelling component for base/plinth									see page 546
Also required									
Side panels for protection category	IP 55	2	8106.235	8106.235	8106.235	8108.235	8108.235	8108.235	567
	IP 55/sealed	1	9671.636	9671.646	9671.666	9671.638	9671.648	9671.668	622
Roof plates for protection category/design	IP 43/vented	1	9671.736	9671.746	9671.766	9671.738	9671.748	9671.768	622
	IP 2X/vented	1	–	9671.846	9660.235	–	9671.848	9659.525	622
Roof plates for cable entry gland	IP 55	1	9671.536	9671.546	9665.903	9671.538	9671.548	9671.568	622
Roof plates with pressure relief function		1	–	9671.446	9660.935	–	9671.448	9671.468	622
Front trim panels, top 300 mm/bottom 100 mm for protection category	IP 54/sealed	1 set	–	9672.014	9672.016	–	9672.014	9672.016	593
	IP 2X/vented	1 set	–	9672.034	9672.036	–	9672.034	9672.036	593
Front trim panels, top 100 mm/bottom 300 mm for protection category	IP 54/sealed	1 set	–	9672.024	9672.026	–	9672.024	9672.026	593
	IP 2X/vented	1 set	–	9672.044	9672.046	–	9672.044	9672.046	593
Upgrade kit for front trim panels 300/100 mm IP 2X	IP 43	1 set	–	9672.054	9672.056	–	9672.054	9672.056	593
Partial doors for clearance height with front trim panel 300/100 mm		1	–	9671.156	9671.176	–	9671.156	9671.176	592
Angular baying brackets		4	8800.430	8800.430	8800.430	8800.430	8800.430	8800.430	579
Baying connectors, external		6	8800.490	8800.490	8800.490	8800.490	8800.490	8800.490	578
Accessories									
Enclosure configuration									see page 592
Compartment configuration									see page 345
Alternative lock systems									see page 600

3 SV-TS 8 cable chamber enclosures (height 2200 mm)

Width mm	Packs of	300	400	600	300	400	600	Page	
Height mm		2200	2200	2200	2200	2200	2200		
Depth mm		600	600	600	800	800	800		
Model No. SV	1	9670.336	9670.436	9670.636	9670.338	9670.438	9670.638		
Door(s)		1	1	1	1	1	1		
Weight (kg)		47.8	57.3	75.8	50.6	61.0	80.7		
Base/plinth									
Components front and rear	Height 100 mm	1 set	8601.915	8601.400	8601.600	8601.915	8601.400	8601.600	543
	Height 200 mm	1 set	8602.915	8602.400	8602.600	8602.915	8602.400	8602.600	543
Trim panels, sides	Height 100 mm	1 set	8601.060	8601.060	8601.060	8601.080	8601.080	8601.080	544
	Height 200 mm	1 set	8602.060	8602.060	8602.060	8602.080	8602.080	8602.080	544
Levelling component for base/plinth									see page 546
Also required									
Side panels for protection category	IP 55	2	8126.235	8126.235	8126.235	8128.235	8128.235	8128.235	567
	IP 55/sealed	1	9671.636	9671.646	9671.666	9671.638	9671.648	9671.668	622
Roof plates for protection category/design	IP 43/vented	1	9671.736	9671.746	9671.766	9671.738	9671.748	9671.768	622
	IP 2X/vented	1	–	9671.846	9660.235	–	9671.848	9659.525	622
Roof plates for cable entry gland	IP 55	1	9671.536	9671.546	9665.903	9671.538	9671.548	9671.568	622
Roof plates with pressure relief function		1	–	9671.446	9660.935	–	9671.448	9671.468	622
Front trim panels, top 300 mm/bottom 100 mm for protection category	IP 54/sealed	1 set	–	9672.014	9672.016	–	9672.014	9672.016	593
	IP 2X/vented	1 set	–	9672.034	9672.036	–	9672.034	9672.036	593
Front trim panels, top 100 mm/bottom 300 mm for protection category	IP 54/sealed	1 set	–	9672.024	9672.026	–	9672.024	9672.026	593
	IP 2X/vented	1 set	–	9672.044	9672.046	–	9672.044	9672.046	593
Upgrade kit for front trim panels 300/100 mm IP 2X	IP 43	1 set	–	9672.054	9672.056	–	9672.054	9672.056	593
Partial doors for clearance height with front trim panel 300/100 mm		1	–	9671.158	9671.178	–	9671.158	9671.178	592
Angular baying brackets		4	8800.430	8800.430	8800.430	8800.430	8800.430	8800.430	579
Baying connectors, external		6	8800.490	8800.490	8800.490	8800.490	8800.490	8800.490	578
Accessories									
Enclosure configuration									see page 592
Compartment configuration									see page 345
Alternative lock systems									see page 600