

TopConsole system TP

Accessories

Trim panel

for pedestal

For covering the complete top opening when using the pedestal on its own.

Material:

- Sheet steel

Surface finish:

- Textured paint

Colour:

- RAL 7035

Protection category IP to IEC 60 529:

- IP 55

NEMA protection category:

- NEMA 12

For pedestal		Model No.
Width mm	Depth mm	
600	400	5001.130
800		5001.140
1200		5001.160
1600		6730.030
600	500	6730.100
800		6730.110
1200		6730.120
1600		6730.130

Supply includes:

- Assembly parts



TP aluminium strip

For retrospective external mounting on:

- TP three-part/two-part
- TP one-piece console
- May be mounted on all enclosures/covers with 20 mm fold height (max. metal thickness 2 mm)

Length: 1750 mm

(Easily cut to length for other dimensions)

Sufficient for desk sections and consoles:

- 3 x width 600 mm
- 2 x width 800 mm
- 1 x width 1000 mm + 1 x width 600 mm
- 1 x width 1200 mm
- 1 x width 1600 mm

Length mm	Model No.
1750	6731.120

Material:

- Aluminium strip: Extruded aluminium section
- Cover caps: Plastic

Surface finish:

- Aluminium strip: Natural anodised

Colour:

- Cover caps: RAL 7035

Supply includes:

- 1 aluminium section
- 6 plastic cover caps
- Drilling template
- Assembly parts



Drawer

for TP universal console

For mouse and keyboard with a maximum width of 500 mm. A high level of protection is retained, even with the flap open.

Material:

- Sheet steel

Surface finish:

- Textured paint

Colour:

- RAL 7035

Protection category IP to IEC 60 529:

- IP 55

NEMA protection category:

- NEMA 12

Supply includes:

- Assembly parts

Height mm	Model No.
200	4757.500



Accessories:

- Standard double-bit lock insert may be exchanged for other 27 mm lock inserts, type A, see page 570 or plastic handle, type B, see page 569



Desk section

For installing display and control components and a keyboard. Closed at the side and front. Trim panels for top and bottom.

Material:

- Sheet steel

Surface finish:

- Dipcoat-primed, powder-coated on the outside, textured paint

Colour:

- RAL 7035

Height mm	Model No.
200	2696.500

Protection category IP to IEC 60 529:

- IP 55

NEMA protection category:

- NEMA 12

Supply includes:

- Assembly parts

