



System accessories Page 507 KL sheet steel Page 30 KL for potentially explosive areas Page 192 KL Hygienic Design Page 170

Material:

- Enclosure: Stainless steel 1.4301 (AISI 304)
- Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal

Surface finish:

- Enclosure and cover: Brushed, grain 180

Protection category IP to IEC 60 529:

- IP 66

Protection category NEMA:

- NEMA 4X

Supply includes:

- Enclosure with cover
- Quick-release fastener including plastic bushes

Approvals:

- UL
- CSA
- TÜV
- Germanischer Lloyd
- Russian Maritime Register of Shipping
- Lloyds Register of Shipping
- Bureau Veritas
- VDE

Technical details:

Available on the Internet

Stainless steel

| Width mm | Packs of | 150 | 150 | 300 | 200 | 200 | Page |
|-----------------------------------|----------|-----------------|-----------------|-----------------|-----------------|-----------------|------|
| Height mm | | 150 | 150 | 150 | 200 | 200 | |
| Depth mm | | 80 | 120 | 80 | 80 | 120 | |
| Material thickness - enclosure mm | | 1.25 | 1.25 | 1.25 | 1.25 | 1.25 | |
| Material thickness - cover mm | | 1.25 | 1.25 | 1.25 | 1.25 | 1.25 | |
| Model No. | 1 pc(s). | 1521.010 | 1527.010 | 1522.010 | 1523.010 | 1528.010 | |
| Weight kg | | 1.3 | 1.6 | 1.8 | 1.8 | 2.2 | |
| Number of quick-release fasteners | | 4 | 4 | 4 | 4 | 4 | |

Accessories

| | | | | | | | |
|--------------------------|-----------|----------|----------|----------|----------|----------|-----|
| Mounting plates | 1 pc(s). | 1560.700 | 1560.700 | 1561.700 | 1562.700 | 1562.700 | 591 |
| Wall mounting bracket | 4 pc(s). | 1594.000 | 1594.000 | 1594.000 | 1594.000 | 1594.000 | 587 |
| Wall angle | 4 pc(s). | 2583.010 | 2583.010 | 2583.010 | 2583.010 | 2583.010 | 588 |
| Pole clamp | 1 set(s) | 2584.000 | 2584.000 | 2584.000 | 2584.000 | 2584.000 | 589 |
| Support rails TS 35/7.5 | 10 pc(s). | 2314.000 | 2314.000 | 2316.000 | 2315.000 | 2315.000 | 614 |
| Cover hinge | 2 pc(s). | 1592.010 | 1592.010 | 1592.010 | 1592.010 | 1592.010 | 574 |
| Pressure relief stoppers | 5 pc(s). | 2459.500 | 2459.500 | 2459.500 | 2459.500 | 2459.500 | 533 |

Stainless steel

| Width mm | Packs of | 300 | 300 | 400 | 300 | 400 | Page |
|-----------------------------------|----------|-----------------|-----------------|-----------------|-----------------|-----------------|------|
| Height mm | | 200 | 200 | 200 | 300 | 300 | |
| Depth mm | | 80 | 120 | 120 | 120 | 120 | |
| Material thickness - enclosure mm | | 1.25 | 1.25 | 1.25 | 1.25 | 1.25 | |
| Material thickness - cover mm | | 1.25 | 1.25 | 1.25 | 1.25 | 1.25 | |
| Model No. | 1 pc(s). | 1524.010 | 1529.010 | 1525.010 | 1526.010 | 1530.010 | |
| Weight kg | | 2.4 | 2.9 | 3.6 | 3.9 | 4.6 | |
| Number of quick-release fasteners | | 4 | 4 | 4 | 4 | 4 | |

Accessories

| | | | | | | | |
|--------------------------|-----------|----------|----------|----------|----------|----------|-----|
| Mounting plates | 1 pc(s). | 1563.700 | 1563.700 | 1564.700 | 1567.700 | 1568.700 | 591 |
| Wall mounting bracket | 4 pc(s). | 1594.000 | 1594.000 | 1594.000 | 1594.000 | 1594.000 | 587 |
| Wall angle | 4 pc(s). | 2583.010 | 2583.010 | 2583.010 | 2583.010 | 2583.010 | 588 |
| Pole clamp | 1 set(s) | 2584.000 | 2584.000 | 2584.000 | 2584.000 | 2584.000 | 589 |
| Support rails TS 35/7.5 | 10 pc(s). | 2316.000 | 2316.000 | 2317.000 | 2316.000 | 2316.000 | 614 |
| Cover hinge | 2 pc(s). | 1592.010 | 1592.010 | 1592.010 | 1592.010 | 1592.010 | 574 |
| Pressure relief stoppers | 5 pc(s). | 2459.500 | 2459.500 | 2459.500 | 2459.500 | 2459.500 | 533 |