

Viewing panels/operating panels

Viewing window

For mounting on

- AE instead of door
- Surfaces

Max. installation depth: (depth -4 mm)

Visible area: (width -60 mm) x (height -60 mm)

Material:

- Frame: Aluminium, natural anodised.
- Glass panel: Acrylic

Protection category IP to IEC 60 529:

- IP 54

Supply includes:

- Plastic handle with lock insert no. 3524 E.

Depth = 34 mm

For use as door variant with	Width mm	Height mm	Model No.
1050.500, 1350.500 1007.600	497	497	2733.000
-	597	197	2734.000
1039.500, 1339.500 1009.600, 7641.000	597	377	2730.000
1010.500, 1054.500 1060.500, 1360.500 7643.000	597	597	2731.000
1012.500, 1076.500 1376.500, 7645.000	597	757	2732.000

Depth = 60 mm

For use as door variant with	Width mm	Height mm	Model No.
1050.500, 1350.500 1007.600	497	497	2763.000
1039.500, 1339.500 1009.600, 7641.000	597	377	2760.000
1010.500, 1054.500 1060.500, 1360.500 7643.000	597	597	2761.000
1012.500, 1076.500 1376.500, 7645.000	597	757	2762.000



Horizontally hinged FT stay

A gas pressurised spring holds the viewing window securely open (top or side).

When the viewing window is closed, the gas pressurised spring disappears into the frame section.

Packs of	Model No.
2 pc(s).	2772.000



Acrylic glazed cover

With security lock, lock no. 3524 E

Material:

- Frame:
Extruded aluminium sections with die-cast corner pieces
- Glass panel: Smoked acrylic

Protection category IP to IEC 60 529:

- IP 54

Acrylic glazed covers, 482.6 mm (19')

U	Width mm	Height mm	Depth mm	Model No.
3	320	158	47.5	2780.000
3	534	158	47.5	2781.000
6	534	291.5	47.5	2782.000
9	534	425	47.5	2796.000

Max. installation depth: 43 mm

Visible area:

(width -40 mm) x (height -20.5 mm)

Metric acrylic glazed covers

Width mm	Height mm	Depth mm	Model No.
400	200	47.5	2784.000
400	400	47.5	2785.000
500	200	47.5	2786.000
500	400	47.5	2787.000
600	200	47.5	2788.000
600	400	47.5	2789.000

Max. installation depth: 43 mm

Visible area: (width -40 mm) x (height -20.5 mm)

