

482.6 mm (19") installation system

482.6 mm (19") installation



Air baffle plates

for TS IT 482.6 mm (19") mounting angles

- To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system
- With all-round brush strip for collision-free shielding with installed rail systems on the outer mounting level

Material:

- Sheet steel
- Plastic, UL 94-V0

Surface finish:

- Spray-finished

Colour:

- RAL 9005

Supply includes:

- Assembly parts

For enclosure width mm	For enclosure height mm	Product-specific scope of supply	Packs of	Model No.
600	2000	-	1 pc(s).	5501.805
800	2000	6 blanking panels, 1 U	1 pc(s).	5501.815
600	2200	-	1 pc(s).	5501.825
800	2200	6 blanking panels, 1 U	1 pc(s).	5501.835



Air baffle plates

for TS IT 482.6 mm (19") mounting frames

With all-round brush strip for collision-free shielding with installed rail systems on the outer mounting level.

Applications:

- To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system

Material:

- Sheet steel
- Blanking panel: Plastic, to UL 94-V0
- Brush strip: Plastic, UL 94-V0

Surface finish:

- Spray-finished

Colour:

- RAL 9005

Supply includes:

- Air baffle plate with all-round brush strip
- Assembly parts

For enclosure width mm	For enclosure height mm	Product-specific scope of supply	Packs of	Model No.
600	1200	-	1 pc(s).	5501.855
800	1200	1 blanking panel, 3 U	1 pc(s).	5501.865
600	1800	-	1 pc(s).	5501.875
800	1800	2 blanking panels, 3 U	1 pc(s).	5501.885
600	2000	-	1 pc(s).	5501.905
800	2000	2 blanking panels, 3 U	1 pc(s).	5501.915
600	2200	-	1 pc(s).	5501.925
800	2200	2 blanking panels, 3 U	1 pc(s).	5501.935



482.6 mm (19") air duct

for horizontal air routing

Air duct, passive, for cold air intake to 482.6 mm (19") IT equipment installed at the rear of server racks which draws in air from the front.

Benefits:

- For superior air infeed to the rear 482.6 mm (19") components
- Integral brush strip for cable entry of 482.6 mm (19") IT equipment
- Supports front-to-back air routing
- Depth-variable

Material:

- Sheet steel, spray-finished

Colour:

- RAL 9005

Width mm	Height U	Depth mm	Packs of	Model No.
482.6	1	223 - 356	1 pc(s).	3301.391

