



System accessories Page 613 **Compartment configuration** Page 367

Material and surface finish:

- Enclosure frame: Sheet steel, 1.5 mm, dipcoat-primed
- Roof: Sheet steel, 1.5 mm, zinc-plated
- Door: Sheet steel, 2 mm, dipcoat-primed, powder-coated on the outside, textured paint
- Rear panel: Sheet steel, 1.5 mm, dipcoat-primed, powder-coated on the outside, textured paint
- Gland plates: Sheet steel, 1.5 mm, zinc-plated
- Punched section without mounting flange: Sheet steel, zinc-plated

Colour:

- RAL 7035

Basis of test:

- IEC 61 439-1/-2
- IEC 61 641

Protection category IP to IEC 60 529:

- Up to IP 3X, depending on the panels

Supply includes:

- Enclosure frame with r/h door hinge, left side open
- Roof
- Rear panel
- Three-piece gland plates
- Lock: 3 mm double-bit
- 4 eyebolts
- Locating frame for disconnectors with fuses (brands ABB SlimLine/Jean Müller SASIL)

Fuse-switch-disconnector enclosures

Width mm	Packs of	1000	1200	1000	1200	Page
Height mm		2000	2000	2200	2200	
Depth mm		600	800	600	800	
Model No.	1 pc(s).	9670.005	9670.107	9670.025	9670.127	
Accessories						
Side panels, screw-fastened, sheet steel	2 pc(s).	8106.235	8108.235	8126.235	8128.235	643
Base/plinth components, front and rear, 100 mm	2 pc(s).	8601.000	8601.200	8601.000	8601.200	619
Base/plinth trim panels, side, 100 mm	2 pc(s).	8601.060	8601.080	8601.060	8601.080	620
Base/plinth components, front and rear, 200 mm	2 pc(s).	8602.000	8602.200	8602.000	8602.200	619
Base/plinth trim panels, side, 200 mm	2 pc(s).	8602.060	8602.080	8602.060	8602.080	620
Levelling feet	4 pc(s).	4612.000	4612.000	4612.000	4612.000	628
Angular baying bracket	4 pc(s).	8800.430	8800.430	8800.430	8800.430	655
Baying connector, external	6 pc(s).	8800.490	8800.490	8800.490	8800.490	654
Roof plates IP 2X with ventilation hole	1 pc(s).	9660.255	9659.555	9660.255	9659.555	693