






# RiLine accessories

## Busbars

### PLS special busbars E-Cu

Technical information:  
Available on the Internet.

#### For system PLS 800, bar thickness 5 mm, bar cross-section 300 mm<sup>2</sup>






For enclosure width mm	Length mm	E-Cu tin-plated <sup>1)</sup>	Approvals	Packs of	Model No. SV	Page
600	495	–		3	<b>3524.000</b>	
600	495	■	–	3	<b>3524.200</b>	
800	695	–		3	<b>3525.000</b>	
800	695	■	–	3	<b>3525.200</b>	
1000	895	–		3	<b>3525.010</b>	
1000	895	■	–	3	<b>3525.210</b>	
1200	1095	–		3	<b>3526.000</b>	
1200	1095	■	–	3	<b>3526.200</b>	
variable	2400	–		1	<b>3509.000</b>	
variable	2400	■	–	1	<b>3509.200</b>	

#### Accessories

PLS busbar connector (single connection)	3	3504.000	313
PLS busbar connector (bayed connection)	3	3505.000	313
PLS expansion connectors	3	9320.060	313

<sup>1)</sup> Extended delivery times.

#### For system PLS 1600, bar thickness 10 mm, bar cross-section 900 mm<sup>2</sup>

For enclosure width mm	Length mm	E-Cu tin-plated <sup>1)</sup>	Approvals	Packs of	Model No. SV	Page
600	495	–		3	<b>3527.000</b>	
600	495	■	–	3	<b>3527.200</b>	
800	695	–		3	<b>3528.000</b>	
800	695	■	–	3	<b>3528.200</b>	
1000	895	–		3	<b>3528.010</b>	
1000	895	■	–	3	<b>3528.210</b>	
1200	1095	–		3	<b>3529.000</b>	
1200	1095	■	–	3	<b>3529.200</b>	
variable	2400	–		1	<b>3516.000</b>	
variable	2400	■	–	1	<b>3516.200</b>	

#### Accessories

PLS busbar connector (single connection)	3	3514.000	313
PLS busbar connector (bayed connection)	3	3515.000	313
PLS expansion connectors	3	9320.070	313

<sup>1)</sup> Extended delivery times.

