

# Connection block



**Busbar system** Page 96 **Connection block** Page 99 **Component adaptor** Page 100 **NH slimline switch-disconnectors** Page 102

For connecting cables and laminated copper bars.

**Further technical information:**  
Available on the Internet

**Material:**

- Sheet steel, zinc-plated
- E-Cu, tin-plated

Rated current max. A	Packs of	1000	1600	1600	Page
Rated operating voltage V, ~		690, 1~	690, 1~	690, 1~	
Cable outlet		Top/bottom	Top/bottom	Top/bottom	
Type of connection		Box terminal	-	Ring terminal M12	
Number of connection cables max.		2	-	4	
Connection of round conductors mm <sup>2</sup>		185 - 300	-	240	
Clamping area for laminated copper bars, W x H (for 10 mm bar thickness) mm		-	80 x 20	-	
Width mm		98	98	98	
For bar thickness mm		10	10	10	
<b>Model No.</b>	1 pc(s).	<b>9677.915</b>	<b>9677.910</b>	<b>9677.920</b>	
<b>Also required</b>					
Contact hazard protection cover plate	1 pc(s).	9677.925	9677.925	9677.925	110