

Roof-mounted fans, roof ventilation



Climate control accessories Page 369

Material:

- Sheet steel, spray-finished

Colour:

- RAL 7035

Protection category IP to IEC 60 529:

- IP 43

Supply includes:

- Unit ready for connection with built-in radial fan
- Sealing and assembly parts
- Connection cable (3 m)
- Drilling template

Note:

- Via additional installation of the filter holder with filter mat, a protection category of IP 44 is achieved with roof vent 3148.007

Technical details:

Available on the Internet

Air throughput 360 m³/h

Model No.	Packs of	3148.007	3149.007	3169.007	Page
Rated operating voltage V, ~, Hz		without fan motor	230, 1~, 50/60	115, 1~, 50/60	
Air throughput, unimpeded air flow m³/h		-	360	360	
Rated current A		-	0.2	0.55	
Power consumption W		-	42	65	
Width mm		420	420	420	
Height mm		65	95	95	
Depth mm		340	340	340	
Required mounting cut-out mm		345 x 265	345 x 265	345 x 265	
Operating temperature range		-10°C...+60°C	-10°C...+60°C	-10°C...+60°C	
Noise level dB(A)		-	53	53	
Weight kg		6.8	7.8	7.8	
Accessories					
Digital enclosure internal temperature display and thermostat	1 pc(s).	-	3114.200	3114.200	379
Enclosure internal thermostat	1 pc(s).	-	3110.000	3110.000	379
Filter holder	1 pc(s).	3175.000	-	-	373