


SERIES 72



SIGMA ELASTIC RUBBER WHEELS CAST IRON CENTRE SWIVEL TOP PLATE BRACKET TYPE M

Wheel description




Tread: Sigma Elastic rubber tread; hardness 70 +/-3 Shore A.

Centre: cast iron.

Hub: Hub: The housing is obtained by moulding and turning and contains ball bearings series Z.

Bracket description

Medium duty racket type M (max. load capacity 500 daN)



- 1) **Plate:** electrolytically galvanised steel plate
 - 2) **Fork:** electrolytically galvanised steel plate
 - 3) **Ball Racing Ring:** electrolytically galvanised steel plate
 - 4) **King Pin:** incorporated in top plate and cold riveted
 - 5) **Swivel actions:** double ring of greased balls
 - 6) **Dust seal:** blue polyethylene
- Finishing:** electrolytic galvanisation
Fitting: top plate