

## SERIES 61

### INJECTION POLYURETHANE WHEELS WITH POLYAMIDE 6 CENTRE



#### Wheel description

Injection polyurethane tread, hardness 80 Shore A. Polyamide 6 centre.

#### Hub

The hub is available with plain bearing, with roller bearing, with stainless steel roller bearing.

**Diameters:** 80-200 mm

**Carrying capacities:** 75-300 daN

### Fittings with swivel, fixed and swivel with brake brackets



#### Standard duty brackets type NL - NLX

Max. carrying capacity 400 daN – available diameters 80-300 mm

Models available: with top plate fastening, with bolt hole

Suitable brakes: front-locking and central (hexagonal) brake systems

### Uses

#### Environments

Suitable for environment with atmospheric agents, alcohol and glycol; not suitable for applications where mineral and organic acids, base solutions and saturated vapour are present.

Usage temperatures: from -15 °C to +70 °C

#### Floors



#### Handling

