

SERIES 37

GREY RUBBER INSTITUTIONAL WHEELS, POLYAMIDE CENTRE WITH THREADGUARDS



Wheel description

Grey non-marking rubber tread; polyamide centre with threadguards.

Hub

The hub is available with plain bore.

Diameters: 50-125 mm

Carrying capacities: 35- 80 daN

Fittings with swivel, fixed and swivel with brake brackets



Swivel top plate brackets

Top carrying capacity 80 daN
Fitted with front brake



Swivel bolt hole brackets

Top carrying capacity 80 daN
Fitted with front brake



Swivel brackets with stem

Top carrying capacity 80 daN
Fitted with front brake

Uses

Environments

Suitable for humid environments, with medium-harsh chemicals; not suitable for applications where organic solvents, chlorinated substances, hydrocarbons and mineral oils are present; is used for home and institutional applications, with light and standard carrying capacity.

Typical usage: office furniture, food charts, electro-medical equipments.

Usage temperatures: from 0°C a +40°C

Floors



Handling

