

SERIES 77

“TR POLYURETHANE” TRANSPALLET ROLLERS, POLYAMIDE 6 CENTRE



Roller description

“TR” polyurethane transpallet roller, hardness 95 +/- 3 Shore A, excellent rolling resistance and elasticity, good resistance to wear and to tearing. Polyamide 6 centre.

Hub

The housing is obtained by moulding and turning and contains ball bearings series Z. The hub is available also without bearings.

Diameters: 82-85 mm

Carrying capacities: 450-600 daN

Uses

Environments

The series is suitable for use in industrial environments for carrying medium-heavy loads, including with mixed outdoor-indoor use. Can be used at speeds of up to 16 km/h; possibility of using for mechanised towing.

Usage temperatures: from -20 °C to +80 °C

Floors



Handling

