



## Base plates ALUFIX ECO



## Base plates

### AF25 ECO, A=25

Nr.	A x B x C	
21488-E	25 x 100 x 125	500
28032-E	25 x 100 x 150	600
21350-E	25 x 150 x 150	900
21352-E	25 x 150 x 200	1.200
21354-E	25 x 150 x 250	1.500
21356-E	25 x 200 x 200	1.600
28033-E	25 x 200 x 300	2.600

### AF40 ECO, A=40,

Nr.	A x B x C	
22862-E	40 x 160 x 200	2.000
22861-E	40 x 160 x 240	2.500
22860-E	40 x 200 x 200	2.600
22842-E	40 x 200 x 240	3.100
22843-E	40 x 200 x 320	4.100
21259-E	40 x 200 x 360	4.600
22851-E	40 x 200 x 400	5.200
21266-E	40 x 320 x 320	6.500

### AF50 ECO, A=50

Nr.	A x B x C	
28100-E	50 x 200 x 250	4.000
27857-E	50 x 200 x 300	5.000
28102-E	50 x 250 x 250	5.000
28104-E	50 x 250 x 500	10.000
28105-E	50 x 300 x 300	7.200
28107-E	50 x 300 x 400	10.000
28109-E	50 x 300 x 500	12.000
28111-E	50 x 400 x 400	13.000
28113-E	50 x 400 x 600	24,000