


Słup prowadzący

Leader pin

SLE



Uwaga: Dostępne także z powłoką DLC.
W celu zamówienia skontaktuj się z nami.
 Note: Available with DLC coating. Contact FCPK for details.

d	d1	d2	s	f	l1	l	L	NR KAT.	NR KAT.
10	14	16	3	3	4	12	25		SLE-10012025
							45		SLE-10012045
							65		SLE-10012065
						17	20		SLE-10017020
							30		SLE-10017030
							50		SLE-10017050
							70		SLE-10017070
						22	25		SLE-10022025
							35		SLE-10022035
							55		SLE-10022055
							75		SLE-10022075
							95		SLE-10022095
						27	20		SLE-10027020
							30		SLE-10027030
							50		SLE-10027050
							70		SLE-10027070
							90		SLE-10027090
						36	25		SLE-10036025
							45		SLE-10036045
							65		SLE-10036065
85		SLE-10036085							
46	30		SLE-10046030						
	45		SLE-10046045						
	70		SLE-10046070						
56	35		SLE-10056035						
	60		SLE-10056060						

Słup prowadzący

Leader pin

SLE

d	d1	d2	s	f	l1	l	L	NR KAT.	NR KAT.
14/15	20	25	6	9	7	17	35	SLE-14017035	SLE-15017035
							55	SLE-14017055	SLE-15017055
							75	SLE-14017075	SLE-15017075
							95	SLE-14017095	SLE-15017095
						22	30	SLE-14022030	SLE-15022030
							50	SLE-14022050	SLE-15022050
							70	SLE-14022070	SLE-15022070
							90	SLE-14022090	SLE-15022090
							110	SLE-14022110	SLE-15022110
							125	SLE-14022125	SLE-15022125
						27	150	SLE-14022150	SLE-15022150
							30	SLE-14027030	SLE-15027030
							45	SLE-14027045	SLE-15027045
							65	SLE-14027065	SLE-15027065
							85	SLE-14027085	SLE-15027085
							105	SLE-14027105	SLE-15027105
							125	SLE-14027125	SLE-15027125
						36	145	SLE-14027145	SLE-15027145
							165	SLE-14027165	SLE-15027165
							35	SLE-14036035	SLE-15036035
							55	SLE-14036055	SLE-15036055
							75	SLE-14036075	SLE-15036075
							95	SLE-14036095	SLE-15036095
						46	125	SLE-14036125	SLE-15036125
							155	SLE-14036155	SLE-15036155
							35	SLE-14046035	SLE-15046035
							45	SLE-14046045	SLE-15046045
							65	SLE-14046065	SLE-15046065
							85	SLE-14046085	SLE-15046085
							105	SLE-14046105	SLE-15046105
						56	125	SLE-14046125	SLE-15046125
							145	SLE-14046145	SLE-15046145
							35	SLE-14056035	SLE-15056035
							55	SLE-14056055	SLE-15056055
							75	SLE-14056075	SLE-15056075
						66	95	SLE-14056095	SLE-15056095
							135	SLE-14056135	SLE-15056135
							55	SLE-14066055	SLE-15066055
							65	SLE-14066065	SLE-15066065
						76	95	SLE-14066095	SLE-15066095
							125	SLE-14066125	SLE-15066125
							55	SLE-14076055	SLE-15076055
						86	95	SLE-14076095	SLE-15076095
							55	SLE-14086055	SLE-15086055
96	95	SLE-14086095	SLE-15086095						
	55	SLE-14096055	SLE-15096055						
116	95	SLE-14096095	SLE-15096095						
	75	SLE-14116075	SLE-15116075						

Słup prowadzący

Leader pin

SLE

d	d1	d2	s	f	l1	l	L	NR KAT.	NR KAT.
18/20	26	31	6	9	7	17	35	SLE-18017035	SLE-20017035
							55	SLE-18017055	SLE-20017055
							75	SLE-18017075	SLE-20017075
							120	SLE-18017120	SLE-20017120
						22	35	SLE-18022035	SLE-20022035
							45	SLE-18022045	SLE-20022045
							65	SLE-18022065	SLE-20022065
							85	SLE-18022085	SLE-20022085
							115	SLE-18022115	SLE-20022115
						27	35	SLE-18027035	SLE-20027035
							45	SLE-18027045	SLE-20027045
							65	SLE-18027065	SLE-20027065
							85	SLE-18027085	SLE-20027085
							105	SLE-18027105	SLE-20027105
							125	SLE-18027125	SLE-20027125
							165	SLE-18027165	SLE-20027165
							225	SLE-18027225	SLE-20027225
						36	245	SLE-18027245	SLE-20027245
							35	SLE-18036035	SLE-20036035
							55	SLE-18036055	SLE-20036055
							75	SLE-18036075	SLE-20036075
							95	SLE-18036095	SLE-20036095
							115	SLE-18036115	SLE-20036115
							135	SLE-18036135	SLE-20036135
							165	SLE-18036165	SLE-20036165
						46	225	SLE-18036225	SLE-20036225
							255	SLE-18036255	SLE-20036255
							35	SLE-18046035	SLE-20046035
							45	SLE-18046045	SLE-20046045
							65	SLE-18046065	SLE-20046065
							85	SLE-18046085	SLE-20046085
							105	SLE-18046105	SLE-20046105
							135	SLE-18046135	SLE-20046135
						56	165	SLE-18046165	SLE-20046165
							245	SLE-18046245	SLE-20046245
							35	SLE-18056035	SLE-20056035
							55	SLE-18056055	SLE-20056055
							75	SLE-18056075	SLE-20056075
						66	95	SLE-18056095	SLE-20056095
							155	SLE-18056155	SLE-20056155
35	SLE-18066035	SLE-20066035							
55	SLE-18066055	SLE-20066055							
75	SLE-18066075	SLE-20066075							
76	95	SLE-18066095	SLE-20066095						
	145	SLE-18066145	SLE-20066145						
	55	SLE-18076055	SLE-20076055						
	75	SLE-18076075	SLE-20076075						
							95	SLE-18076095	SLE-20076095
							135	SLE-18076135	SLE-20076135

Słup prowadzący

Leader pin

SLE

d	d1	d2	s	f	l1	l	L	NR KAT.	NR KAT.
18/20	26	31	6	9	7	86	55	SLE-18086055	SLE-20086055
							75	SLE-18086075	SLE-20086075
							95	SLE-18086095	SLE-20086095
							125	SLE-18086125	SLE-20086125
						96	55	SLE-18096055	SLE-20096055
							95	SLE-18096095	SLE-20096095
						116	75	SLE-18116075	SLE-20116075
							115	SLE-18116115	SLE-20116115
						136	135	SLE-18136135	SLE-20136135
						22/24	30	35	6
55	SLE-22017055	SLE-24017055							
75	SLE-22017075	SLE-24017075							
22	35	SLE-22022035	SLE-24022035						
	55	SLE-22022055	SLE-24022055						
	75	SLE-22022075	SLE-24022075						
	105	SLE-22022105	SLE-24022105						
	130	SLE-22022130	SLE-24022130						
27	35	SLE-22027035	SLE-24027035						
	45	SLE-22027045	SLE-24027045						
	65	SLE-22027065	SLE-24027065						
	85	SLE-22027085	SLE-24027085						
	105	SLE-22027105	SLE-24027105						
	125	SLE-22027125	SLE-24027125						
	165	SLE-22027165	SLE-24027165						
	205	SLE-22027205	SLE-24027205						
	245	SLE-22027245	SLE-24027245						
	285	SLE-22027285	SLE-24027285						
36	35	SLE-22036035	SLE-24036035						
	55	SLE-22036055	SLE-24036055						
	75	SLE-22036075	SLE-24036075						
	95	SLE-22036095	SLE-24036095						
	115	SLE-22036115	SLE-24036115						
	135	SLE-22036135	SLE-24036135						
	165	SLE-22036165	SLE-24036165						
	205	SLE-22036205	SLE-24036205						
	245	SLE-22036245	SLE-24036245						
	285	SLE-22036285	SLE-24036285						
46	35	SLE-22046035	SLE-24046035						
	45	SLE-22046045	SLE-24046045						
	65	SLE-22046065	SLE-24046065						
	85	SLE-22046085	SLE-24046085						
	105	SLE-22046105	SLE-24046105						
	125	SLE-22046125	SLE-24046125						
	165	SLE-22046165	SLE-24046165						
	205	SLE-22046205	SLE-24046205						

Słup prowadzący

Leader pin

SLE

d	d1	d2	s	f	l1	l	L	NR KAT.	NR KAT.
22/24	30	35	6	9	7	56	35	SLE-22056035	SLE-24056035
							55	SLE-22056055	SLE-24056055
							75	SLE-22056075	SLE-24056075
							95	SLE-22056095	SLE-24056095
							115	SLE-22056115	SLE-24056115
							165	SLE-22056165	SLE-24056165
						66	35	SLE-22066035	SLE-24066035
							55	SLE-22066055	SLE-24066055
							75	SLE-22066075	SLE-24066075
							95	SLE-22066095	SLE-24066095
							155	SLE-22066155	SLE-24066155
						76	55	SLE-22076055	SLE-24076055
							75	SLE-22076075	SLE-24076075
							95	SLE-22076095	SLE-24076095
							115	SLE-22076115	SLE-24076115
						86	145	SLE-22076145	SLE-24076145
							55	SLE-22086055	SLE-24086055
							75	SLE-22086075	SLE-24086075
							95	SLE-22086095	SLE-24086095
						96	135	SLE-22086135	SLE-24086135
							55	SLE-22096055	SLE-24096055
							75	SLE-22096075	SLE-24096075
							95	SLE-22096095	SLE-24096095
						116	125	SLE-22096125	SLE-24096125
							75	SLE-22116075	SLE-24116075
							115	SLE-22116115	SLE-24116115
						136	155	SLE-22116155	SLE-24116155
							95	SLE-22136095	SLE-24136095
156	135	SLE-22136135	SLE-24136135						
	155	SLE-22156155	SLE-24156155						
30/32	42	47	6	9	7	22	35	SLE-30022035	SLE-32022035
							75	SLE-30022075	SLE-32022075
							130	SLE-30022130	SLE-32022130
						27	45	SLE-30027045	SLE-32027045
							65	SLE-30027065	SLE-32027065
							105	SLE-30027105	SLE-32027105
							165	SLE-30027165	SLE-32027165
							185	SLE-30027185	SLE-32027185
							245	SLE-30027245	SLE-32027245
						36	285	SLE-30027285	SLE-32027285
							55	SLE-30036055	SLE-32036055
							75	SLE-30036075	SLE-32036075
							95	SLE-30036095	SLE-32036095
							115	SLE-30036115	SLE-32036115
							155	SLE-30036155	SLE-32036155
245	SLE-30036245	SLE-32036245							
285	SLE-30036285	SLE-32036285							

Słup prowadzący

Leader pin

SLE

d	d1	d2	s	f	l1	l	L	NR KAT.	NR KAT.
30/32	42	47	6	9	7	46	45	SLE-30046045	SLE 32046045
							65	SLE-30046065	SLE-32046065
							85	SLE-30046085	SLE-32046085
							105	SLE-30046105	SLE 32046105
							125	SLE-30046125	SLE-32046125
							165	SLE-30046165	SLE-32046165
							245	SLE-30046245	SLE-32046245
							285	SLE-30046285	SLE-32046285
						56	55	SLE-30056055	SLE-32056055
							75	SLE-30056075	SLE-32056075
							95	SLE-30056095	SLE 32056095
							115	SLE-30056115	SLE-32056115
							135	SLE-30056135	SLE-32056135
							175	SLE-30056175	SLE-32056175
							245	SLE-30056245	SLE-32056245
							295	SLE-30056295	SLE-32056295
						66	55	SLE-30066055	SLE-32066055
							75	SLE-30066075	SLE-32066075
							95	SLE-30066095	SLE-32066095
							115	SLE-30066115	SLE-32066115
							135	SLE-30066135	SLE-32066135
							175	SLE30066175	SLE 32066175
							245	SLE-30066245	SLE 32066245
							295	SLE-30066295	SLE-32066295
						76	55	SLE-30076055	SLE-32076055
							75	SLE-30076075	SLE-32076075
							95	SLE-30076095	SLE-32076095
							115	SLE-30076115	SLE-32076115
							155	SLE-30076155	SLE-32076155
							225	SLE-30076225	SLE-32076225
						86	55	SLE-30086055	SLE-32086055
							75	SLE-30086075	SLE-32086075
							95	SLE-30086095	SLE-32086095
							115	SLE-30086115	SLE-32086115
							155	SLE-30086155	SLE-32086155
							225	SLE-30086225	SLE-32086225
						96	55	SLE-30096055	SLE-32096055
							75	SLE-30096075	SLE -32096075
							95	SLE-30096095	SLE-32096095
							115	SLE-30096115	SLE-32096115
							155	SLE-30096155	SLE-32096155
							205	SLE-30096205	SLE-32096205
						116	75	SLE-30116075	SLE-32116075
							115	SLE-30116115	SLE-32116115
							155	SLE-30116155	SLE-32116155
						136	95	SLE-30136095	SLE-32136095
							115	SLE-30136115	SLE-32136115
							155	SLE-30136155	SLE-32136155
156	115	SLE-30156115	SLE-32156115						
	155	SLE-30156155	SLE-32156155						

Słup prowadzący

Leader pin

SLE

d	d1	d2	s	f	l1	l	L	NR KAT.	NR KAT.
30/32	42	47	6	9	7	176	135	SLE-30176135	SLE-32176135
							175	SLE-30176175	SLE-32176175
						196	155	SLE-30196155	SLE-32196155
							195	SLE-30196195	SLE-32196195
40/42	54	60	10	12	7	36	75	SLE-40036075	SLE-42036075
							135	SLE-40036135	SLE-42036135
						46	95	SLE-40046095	SLE-42046095
							165	SLE-40046165	SLE-42046165
						56	75	SLE-40056075	SLE-42056075
							115	SLE-40056115	SLE-42056115
							155	SLE-40056155	SLE-42056155
						66	195	SLE-40056195	SLE-42056195
							75	SLE-40066075	SLE-42066075
							135	SLE-40066135	SLE-42066135
						76	75	SLE-40076075	SLE-42076075
							115	SLE-40076115	SLE-42076115
							175	SLE-40076175	SLE-42076175
						86	75	SLE-40086075	SLE-42086075
							135	SLE-40086135	SLE-42086135
						96	75	SLE-40096075	SLE-42096075
							115	SLE-40096115	SLE-42096115
							155	SLE-40096155	SLE-42096155
						116	95	SLE-40116095	SLE-42116095
							135	SLE-40116135	SLE-42116135
							195	SLE-40116195	SLE-42116195
						136	95	SLE-40136095	SLE-42136095
							135	SLE-40136135	SLE-42136135
							215	SLE-40136215	SLE-42136215
						156	115	SLE-40156115	SLE-42156115
							155	SLE-40156155	SLE-42156155
							215	SLE-40156215	SLE-42156215
						176	135	SLE-40176135	SLE-42176135
							155	SLE-40176155	SLE-42176155
							175	SLE-40176175	SLE-42176175
						196	155	SLE-40196155	SLE-42196155
							195	SLE-40196195	SLE-42196195
							235	SLE-40196235	SLE-42196235
						246	165	SLE-40246165	SLE-42246165
							245	SLE-40246245	SLE-42246245
						50/52	66	71	10
95	SLE-50056095	SLE-52056095							
115	SLE-50056115	SLE-52056115							
155	SLE-50056155	SLE-52056155							
66	75	SLE-50066075	SLE-52066075						
	95	SLE-50066095	SLE-52066095						
	115	SLE-50066115	SLE-52066115						
	155	SLE-50066155	SLE-52066155						
76	75	SLE-50076075	SLE-52076075						
	95	SLE-50076095	SLE-52076095						
	115	SLE-50076115	SLE-52076115						
	155	SLE-50076155	SLE-52076155						
						195	SLE-50076195	SLE-52076195	

Słup prowadzący

Leader pin

SLE

d	d1	d2	s	f	l1	l	L	NR KAT.	NR KAT.
50/52	66	71	10	12	10	86	75	SLE-50086075	SLE-52086075
							95	SLE-50086095	SLE-52086095
							115	SLE-50086115	SLE-52086115
							155	SLE-50086155	SLE-52086155
						96	95	SLE-50096095	SLE-52096095
							115	SLE-50096115	SLE-52096115
							155	SLE-50096155	SLE-52096155
							195	SLE-50096195	SLE-52096195
						116	115	SLE-50116115	SLE-52116115
							155	SLE-50116155	SLE-52116155
							195	SLE-50116195	SLE-52116195
						136	115	SLE-50136115	SLE-52136115
							155	SLE-50136155	SLE-52136155
							195	SLE-50136195	SLE-52136195
						156	135	SLE-50156135	SLE-52156135
							155	SLE-50156155	SLE-52156155
							195	SLE-50156195	SLE-52156195
						176	155	SLE-50176155	SLE-52176155
							195	SLE-50176195	SLE-52176195
							235	SLE-50176235	SLE-52176235
						196	155	SLE-50196155	SLE-52196155
							195	SLE-50196195	SLE-52196195
							235	SLE-50196235	SLE-52196235
						216	155	SLE-50216155	SLE-52216155
							195	SLE-50216195	SLE-52216195
							235	SLE-50216235	SLE-52216235
						236	155	SLE-50236155	SLE-52236155
							195	SLE-50236195	SLE-52236195
							235	SLE-50236235	SLE-52236235
							275	SLE-50236275	SLE-52236275
						256	155	SLE-50256155	SLE-52256155
							195	SLE-50256195	SLE-52256195
235	SLE-50256235	SLE-52256235							
275	SLE-50256275	SLE-52256275							