



平型扭矩蝶形合页





①代号	类型		调整角度	④材质	⑤表面处理/颜色
HGNZYD	阻尼型	锥孔型	任意角度定位型	ZDC	镀砂铬
HGNZYE					喷塑(麻面黑)

⚠未配备安装螺钉, 托盘, 请用户自备。




HGNZYD




HGNZYE


安装图



开孔尺寸



轨迹图



视角标准: 第一视角



①代号 - ②规格
HGNZYE - 40

型号		A	B	A ₁	B ₁	T	d	D	H	扭矩 N·M	负载 (kg)	参考重量 (kg/pcs)	
HGNZYE	②规格												
	40									0.9			
	40A									1.4	25	0.04	
	40B	40	40	25	25	6	5.3	10.6	13.5	1.8			
	40C									2.3			
	40D												
	50												
	50A										1.8	27	0.06
	50B	50	50	30	30	7	6.3	12.8	15	2.3			
	50C										3.4		
	60												
	60A										1.36		
60B	60	60	36	36	8	8.4	17.6	17	2.26	30	0.1		
60C										3.16			
60D										4.07			

型号		扭矩 N·M	参考重量 (kg/pcs)
①代号	②规格		
HGNZYD	30	3±20%	0.16
	50	5±20%	



数量分类	小单	中大单	大单
数量	1~50	51~100	100~
交货期	通常	7工作日	现询



数量	1~9	10~
价格	100%	现询



百万商品齐上线, 获取专属企业折扣, 轻松下单



400-6699-428



www.ant-fa.com