


UITVOERING G / BAUFORM G / MOUNTING STYLE G



TYPE	CILINDER		Afmetingen (mm)														
			R	L2	A	E	K	a2	b2	e1	f1	g1	h1	l	m2	x2	y1
ACDG- 40/	20	22 25	R3/8"	176	50	M16 x 1,5	41	50	25	30	20	19	16	48	67	12	16
ACDG- 50/	25	30 35	R3/8"	200	60	M16 x 1,5	46	55	28	35	25	23	20	57	75	15	16
ACDG- 60/	30	35 40	R1/2"	219	70	M22 x 1,5	53	65	33	40	30	28	22	61	82	16	22
ACDG- 63/	32	35 36	R1/2"	219	75	M22 x 1,5	56	65	33	40	30	28	22	61	82	16	22
ACDG- 65/	30	32 35	R1/2"	219	75	M22 x 1,5	56	65	33	40	30	28	22	61	82	16	22
ACDG- 70/	35	40 45	R1/2"	219	80	M22 x 1,5	58	65	33	40	30	28	22	61	82	16	22
ACDG- 80/	40	45 50	R1/2"	249	95	M28 x 1,5	66	83	41	50	35	30	25	68	93	17	28
ACDG- 90/	45	50 55	R1/2"	249	105	M28 x 1,5	71	83	41	50	35	30	25	68	93	17	28
ACDG-100/	50	55 60	R1/2"	267	115	M35 x 1,5	76	100	50	60	40	35	28	64	101	17	35
ACDG-110/	50	55 60	R1/2"	267	130	M35 x 1,5	84	100	50	60	40	35	28	64	101	17	35
ACDG-120/	60	70 80	R3/4"	320	140	M45 x 1,5	91	123	61	70	50	40	35	73	128	25	45
ACDG-125/	60	70 80	R3/4"	320	145	M45 x 1,5	94	123	61	70	50	40	35	73	128	25	45
ACDG-130/	70	80 85	R3/4"	320	150	M58 x 1,5	96	140	70	70	60	50	44	73	128	25	58
ACDG-140/	70	80 85	R3/4"	392	160	M65 x 1,5	101	164	82	75	70	55	49	108	147	35	65
ACDG-150/	80	85 90	R3/4"	392	170	M65 x 1,5	106	164	82	75	70	55	49	108	147	35	65
ACDG-160/	85	90 100	R1"	477	180	M80 x 2	115	180	90	95	80	60	55	140	177	37	80
ACDG-180/	90	110 140	R1"	532	210	M100 x 2	130	226	113	110	90	65	60	150	207	42	100
ACDG-200/	100	110 125	R1"	597	230	M110 x 2	139	250	125	120	100	70	70	170	237	47	110