


UITVOERING G/G / BAUFORM G/G / MOUNTING STYLE G/G



TYPE CILINDER		Afmetingen (mm)														
		R	L12	A	K	a2	b2	e1	f1	g1	h1	l	m2	x2		
ACDG/G-40/	20 28 25	R3/8"	206	50	41	50	25	30	20	19	16	48	67	12		
ACDG/G-50/	25 30 35	R3/8"	235	60	46	55	28	35	25	23	20	57	75	15		
ACDG/G-60/	30 35 40	R1/2"	259	70	53	65	33	40	30	28	22	61	82	16		
ACDG/G-63/	32 40 45	R1/2"	259	75	56	65	33	40	30	28	22	61	82	16		
ACDG/G-65/	30 40 45	R1/2"	259	75	56	65	33	40	30	28	22	61	82	16		
ACDG/G-70/	35 50 45	R1/2"	259	80	58	65	33	40	30	28	22	61	82	16		
ACDG/G-80/	40 55 60	R1/2"	299	95	66	83	41	50	35	30	25	68	93	17		
ACDG/G-90/	45 60 65	R1/2"	299	105	71	83	41	50	35	30	25	68	93	17		
ACDG/G-100/	50 70 60	R1/2"	327	115	76	100	50	60	40	35	28	64	101	17		
ACDG/G-110/	50 70 60	R1/2"	327	130	84	100	50	60	40	35	28	64	101	17		
ACDG/G-120/	60 85 70	R3/4"	390	140	91	123	61	70	50	40	35	73	128	25		
ACDG/G-125/	60 85 90	R3/4"	390	145	94	123	61	70	50	40	35	73	128	25		
ACDG/G-130/	70 80 85	R3/4"	390	150	96	140	70	70	60	50	44	73	128	25		
ACDG/G-140/	70 90 100	R3/4"	467	160	101	164	82	75	70	55	49	108	147	35		
ACDG/G-150/	80 100 85	R3/4"	467	170	106	164	82	75	70	55	49	108	147	35		
ACDG/G-160/	85 100 90	R1"	572	180	115	180	90	95	80	60	55	140	177	37		
ACDG/G-180/	90 125 140	R1"	642	210	130	226	113	110	90	65	60	150	207	42		
ACDG/G-200/	100 125 140	R1"	717	230	139	250	125	120	100	70	70	170	237	47		