







暗式拉手




①代号	类型 背面形状	安装孔	④材质	⑤表面处理
PHASJH	标准型	4外螺纹	SUS304	拉丝
PHASJI				镜面抛光
PHASJJ				拉丝
PHASJK				烤漆(黑色)
PHASJL				拉丝



PHASJH
PHASJI



PHASJJ
PHASJK
PHASJL



视角标准：第一视角



①代号 - ②A - ③安装方式
PHASJH - A94 - G

①代号	型号			L ₁	E	E ₁	H	H ₁	H ₂	M	开孔尺寸				参考重量 (kg/pcs)	
	②A	③安装方式									X	X ₁	Y	Y ₁		
PHASJH PHASJI	94	G(螺杆型) M(螺母型)		61	60	25	17					76	63	43	32	0.08
	109.5			67.5	64	19.5	5	14	M4	88	73	42	38	0.1		
	138		96	88	35	26						110	99	64	65	0.17
PHASJJ PHASJK PHASJL	100	不带胶垫		70	54	25	20.5	1.5	12	M4	88	73	42	38	0.09	
		无指定(带胶垫) N(不带胶垫)														
		带胶垫														



数量分类	小单	中大单	大单
数量	1~50	51~100	100~
交货期	通常	7工作日	现询



数量	1-9	10~
价格	100%	现询

