


①代号	类型	安装类型	M材质	S表面处理
DTZCWA	滚珠式	外装型	黄铜	-
DTZCWB				镀铬
DTZZWA			锌合金	-
DTZZWB				镀铬
DTZSWA			SUS304	镜面抛光



视角标准：第一视角

G1 手柄/门组件



①代号 - ②L  
DTZSWA - L70

型号		L <sub>1</sub>	L <sub>2</sub>	H <sub>1</sub>	H <sub>2</sub>	H <sub>3</sub>	W <sub>1</sub>	W <sub>2</sub>	d	推入力(kgf)	推出力(kgf)	参考重量(kg/pcs)
①代号	②L											
	40	31	15		10.3		8	7.2	3.5	1.5	0.8	0.02
44	35								4	1.8	1.2	
DTZCWA	49	40	20						3.5	2	1.7	
	50	38	18	2	11	2	9	8	5	2.3	1.8	
	50A	36	20						5	2.6	2	
	60	49	24		13.2		11	9	5	3.2	2.6	
69	59	30		16		13.2	12	5	3.2	2.6	0.06	
DTZCWB	44	35	15	2	9.4	1.7	8	7.5	3.8	1.8	1.2	0.02
	49	40	20		10.6	2	8.8	7.6	5.2	2	1.7	
	60	50	24		13.2	2.2	11.2	10	5.2	2.6	2	
	69	58	30	2.4	15	2.3	13	12	5.2	3.2	2.6	0.07

型号		L <sub>1</sub>	L <sub>2</sub>	H <sub>1</sub>	H <sub>2</sub>	H <sub>3</sub>	W <sub>1</sub>	W <sub>2</sub>	d	推入力(kgf)	推出力(kgf)	参考重量(kg/pcs)
①代号	②L											
	DTZZWA	70	60	30	4	17.5	4	13.5	10.5	4.2	5.7	3.9
DTZZWB	32	25	11	2	9	2	8	8	3.2	1.7	0.8	0.01
	42.5	35	16	2.5	10	2.5	8	7.5	3.2	2	1.3	0.02
	43	34.2	16.5	1.8	10	2.2	8	8	4.2	2	1.3	0.03
	50	40	20	3	12.5	2.5	10	9	4.2	2.3	1.8	0.03
70	60	30	4	17	3	13.5	10.5	4.2	5.7	3.9	0.07	

型号		L <sub>1</sub>	L <sub>2</sub>	H <sub>1</sub>	H <sub>2</sub>	H <sub>3</sub>	W <sub>1</sub>	W <sub>2</sub>	d	推入力(kgf)	推出力(kgf)	参考重量(kg/pcs)
①代号	②L											
	DTZSWA	32	25	11	2	9	2	8	3.2	1.7	0.8	0.012
DTZSWA	43	35	16	2.5	10	2.5	8	7.5	3.2	2	1.3	0.016
	50	40	20	3	12.2	3	10	9	4.2	2.3	1.8	0.028
	70	60	30	4	17	4	13	10.5	4.2	5.7	3.9	0.078



数量分类	小单	中大单	大单
数量	1-50	51-100	101~
交货期	通常	7工作日	现询



数量	1-9	10~
价格	100%	另行报价