




★ 产品特点: 由于实现重量平衡, 适于旋转零件的安装。附件内六角螺栓经过防松处理。



类型	M材质	S表面处理	A附件
SCCBV	一般结构钢	发黑	2个内六角螺栓
SCCEV	一般结构钢	无电解镀锌	2个内六角螺栓 (不锈钢)
SCCNV	不锈钢	-	

▲ 如对防锈有要求, 请优先选用不锈钢材质或无电解镀锌产品。



视角标准: 第一视角

A3 固定环



①代号 - ②D - ③B
SCCBV - D16 - B12

Type	型式		D ₁	M (粗牙螺纹)	d	R	a	T ₁	T ₂
	D	B							
SCCBV SCCEV SCCNV	16	10	35					12	6
		12							
	17	10	40	M5	5.5	4.5		14	7
		12							
	20	10					1.5		
		12							
	25	15	45	M6	6.6	6		15	8
		12							
	30	15	55	M6	6.6	6		17	7
		15							
	35	15	60	M8	9	7		18	10
		20							
40	15		M6	6.6	6	2	20	12	
	18								
50	18	70	M8	9	7		23	13	
	22								
		85	M10	11	9	3	26	16	



交货期 **5** 天发货

数量分类	标准订单	特殊订单
	数量	小单 1-50
交货期	5天发货	另行报价

▲ 常州东莞发货遇特殊期间交期有变更。
▲ 部分型号为5天发货, 请以报价为准。

