



1 代号 - 2 D - 3 t - 4 d - 5 L - 6 链轮齿数 - 7 配套链条  
 GMSX - D50 - t1.5 - d12 - L500 - T14 - 08B

型号		3 t	4 d	5 L	L <sub>1</sub>	6 链轮齿数	7 配套链条	节圆直径 d <sub>1</sub>	A	B	C
GMSX GMS	2 D										
	50	1.5	12	200~1900	L+62	T11	08B	45.08	17	22	
	60	2	12 15		L+63	T14		57.07			
	60	3	15	200~2200							
	76	3		20							18.5
	76	4		20				66.33			
	80	3		20	200~2600	L+69	T13	10A	20	25	
	89	3		20		T15	10B	76.35			
89	4		20								

▲ 不锈钢仅有标注■的尺寸  
 ▲ 使用温度: -20°C~80°C

4 d	M	螺纹深度
12	8	15
15	10	20
20	12	25