

成品孔链轮

08A 系列传动链轮



大批量
订购
bulk order

08A 系列传动链轮



CAD
2D|3D
标准加工
按图定制

代号	材质	热处理	表面处理	附件	附件表面处理
DSFA08AB	45#	齿部高频淬火	无	紧定螺钉	无
DSFB08AB			发黑		发黑
DSFC08AB	304	无	无	不锈钢紧定螺钉	无


产品特点: 产品内孔标准化, 可直接用于现场安装。

对应链条尺寸系列

08A

订购编号示例

1 代号	2 齿数	3 dr
DSFA08AB	14	14



1 代号	2 齿数	主要尺寸					重量 kg	
		3 孔径 dr	节径 D	外径 D ₁	凸台直径 D ₂	总长 L		
DSFA08AB DSFB08AB	▲ 9	10 12 14 15	37.13	42	28	22	5	0.11
	▲ 10	10 12 14 15 16 17 18	41.1	46	32			0.14
	▲ 11	10 12 14 15 16 17 18 19 20	45.08	51	36			0.19
	▲ 12	10 12 14 15 16 17 18 19 20 22	49.07	55	40			0.22
	13	12 14 15 16 17 18 19 20 22 24 25	53.07	59	37			0.23
	14	12 14 15 16 17 18 19 20 22 24 25 28	57.07	63	42			0.28
	15	12 14 15 16 17 18 19 20 22 24 25 28 30	61.08	67	46			0.34
	16	14 15 16 17 18 19 20 22 24 25 28 30 32	65.1	71	50			0.4
	17	14 15 16 17 18 19 20 22 24 25 28 30 32 35	69.12	76	54			0.46
	18	14 15 16 17 18 19 20 22 24 25 28 30 32 35 40	73.14	80	57			0.51
	19	14 15 16 17 18 19 20 22 24 25 28 30 32 35 38 40	77.16	84	62	0.59		
	20		81.18	88	67	0.76		
	21	14 15 16 17 18 19 20 22 24 25 28 30 32 35 38 40 42 45	85.21	92	71	0.85		
	22		89.24	96	75	0.95		
	23		93.27	100	77	1		
	24		97.3	104	63	25	7	0.84
	25		101.33	108				0.88
	26	14 15 16 17 18 19 20 22 24 25 28 30 32 35 38 40 42	105.36	112				0.92
	28		113.43	120				1
	30		121.5	128				1.1
32		129.57	137	1.3				
34		137.64	145	68	28	10	1.3	
35	20 22 24 25 28 30 32 35 40	141.68	149				1.4	
36		145.72	153				1.5	
38	24 25 28 30 32 35 40	153.79	161				1.6	
40	25 28 30 32 35 40	161.87	169				1.7	
40		161.87	169				1.7	
DSFC08AB	▲ 10	12 15 16	41.1	46	32	22	5	0.14
	▲ 11		45.08	51	36			0.19
	▲ 12	15 16 18 20	49.07	55	40			0.22
	13		53.07	59	37			0.23
	14	15 16 18 19 20 22 24 25	57.07	63	42			0.28
	15	15 16 18 19 20 22 24 25 28	61.08	67	46			0.34
	16		65.1	71	50			0.4
	17		69.12	76	54			0.46
	18	15 16 18 19 20 22 24 25 28 30	73.14	80	57			0.51
	19		77.16	84	62			0.59
	20		81.18	88	67	0.76		
	21		85.21	92	71	0.85		
	22		89.24	96	75	0.95		
	23	18 20 22 24 25 28 30	93.27	100	77	1		
	24		97.3	104	63	25	7	0.84
	25		101.33	108				0.88
	26		105.36	112				0.92
	28		113.43	120				1
	30		121.5	128				1.1
	32		129.57	137				1.3
35	20 22 25 30	141.68	149	68	28	10	1.4	
36		145.72	153				1.5	
38		153.79	161				1.6	
40		161.87	169				1.7	
40		161.87	169				1.7	

轴孔加工尺寸

轴孔直径 dr	键槽 bxt ₂	紧定螺钉 M
10	3x1.4	M4
12	4x1.8	M5
14~17	5x2.3	M6
18~22	6x2.8	M6
24~30	8x3.3	M8
32~38	10x3.3	M8
39~44	12x3.3	M8
45	14x3.8	M10

带有▲的产品在轮毂外径上带有槽口, 尺寸如下表

齿数	S	GD
9	5.2	23
10		27
11		31
12		35
12		35

交货期	小单	大单
	1-20	21-
正常	报价	

货期	DSFA08AB	DSFB08AB	DSFC08AB
	3天发货	7天发货	现询