

成品孔链轮

10A 系列传动链轮



大批量
订购
bulk order

10A 系列传动链轮



CAD
2D/3D


标准加工
按图定制

①代号	材质	热处理	表面处理	附件	附件表面处理
DSFA10AB	45#	齿部高频淬火	无	紧定螺钉	无
DSFB10AB			发黑		发黑
DSFC10AB	304	无	无	不锈钢紧定螺钉	无

产品特点: 产品内孔标准化, 可直接用于现场安装。

对应链条尺寸系列
10A

10A 系列



订购编号示例

①代号	②齿数	③dr
DSFA10AB	15	28

键槽中心对准齿尖中心

①代号	②齿数	主要尺寸					重量 kg			
		③孔径 dr			节径 D	外径 D ₁		凸台直径 D ₂	总长 L	a
DSFA10AB DSFB10AB	▲ 9	16 17 18 19			46.42	53	34	25	5	0.2
	▲ 10	15 16 17 18 19 20 22 24 25			51.37	58	40			0.27
	▲ 11	15 16 17 18 19 20 22 24 25 28 30 32			56.35	64	45.5			0.33
	▲ 12	14 15 16 17 18 19 20 22 24 25 28 30 32			61.34	69	50			0.41
	▲ 13	14 15 16 17 18 19 20 22 24 25 28 30 32 35			66.34	74	51			0.46
	14	14 15 16 17 18 19 20 22 24 25 28 30 32 35 38			71.34	79	52		0.52	
	15	14 15 16 17 18 19 20 22 24 25 28 30 32 35 38 40			76.35	84	57		0.62	
	16	14 15 16 17 18 19 20 22 24 25 28 30 32 35 38 40 42 45			81.37	89	62		0.72	
	17	14 15 16 17 18 19 20 22 24 25 28 30 32 35 38 40 42 45 50			86.39	94	67		0.83	
	18	14 15 16 17 18 19 20 22 24 25 28 30 32 35 38 40 42 45 50			91.42	100	72		1	
	19	14 15 16 17 18 19 20 22 24 25 28 30 32 35 38 40 42 45 50			96.45	105		1.1		
	20	17 18 19 20 22 24 25 28 30 32 35 38 40 42 45			101.48	110	73	28	8	1.2
	21	17 18 19 20 22 24 25 28 30 32 35 38 40 42 45			106.51	115				1.2
	22	17 18 19 20 22 24 25 28 30 32 35 38 40 42 45			111.55	120				1.3
	23	17 18 19 20 22 24 25 28 30 32 35 38 40 42 45			116.58	125				1.3
	24	17 18 19 20 22 24 25 28 30 32 35 38 40 42 45			121.62	130				1.4
	25	24 25 28 30 32 35 38 40 45			126.66	135			1.5	
	26	24 25 28 30 32 35 38 40 45			131.7	140			1.5	
	28	24 25 28 30 32 35 38 40 42 45			141.79	150			1.6	
	30	22 25 28 30 32 35 38 40 45			151.87	161			1.8	
32	25 28 30 32 35 38 40 45			161.96	171	1.9				
34	25 28 30 32 35 38 40 45			172.05	181	2.1				
35	25 28 30 32 35 38 40 45			177.1	186	2.2				
DSFC10AB	▲ 10	20 22			51.37	58	40	25	5	0.27
	▲ 11	20 22 24 25			56.35	64	45.5			0.33
	▲ 12	20 22 24 25			61.34	69	50			0.41
	▲ 13	20 22 24 25 28 30			66.34	74	51			0.46
	14	20 22 24 25 28 30			71.34	79	52			0.52
	15	20 22 24 25 28 30 32			76.35	84	57		0.62	
	16	20 22 24 25 28 30 32 38			81.37	89	62		0.72	
	17	20 22 24 25 28 30 32 35 38			86.39	94	67		0.83	
	18	20 22 24 25 28 30 32 35 38 40			91.42	100	72		1	
	19	20 22 24 25 28 30 32 35 38 40			96.45	105			1.1	
	20	20 25 30 35 40			101.48	110	73	28	8	1.2
	21	20 25 30 35 40			106.51	115				1.2
	22	20 25 30 35 40			111.55	120				1.3
	23	20 25 30 35			116.58	125				1.3
	24	20 25 30 35			121.62	130				1.4
	25	20 25 30 35 40			126.66	135			1.5	
	26	20 25 30 35			131.7	140			1.5	
	28	20 25 30 35 40			141.79	150			1.6	
	30	20 25 30 35 40			151.87	161			1.8	
	32	25 30 35			161.96	171			1.9	
35	25 30 35			177.1	186	2.2				

轴孔加工尺寸

轴孔直径 dr	键槽 bxt ₂	紧定螺钉 M
14~17	5x2.3	M6
18~22	6x2.8	M6
24~30	8x3.3	M8
32~38	10x3.3	M8
39~44	12x3.3	M8
45~50	14x3.8	M10

带有▲的产品在轮毂外径上带有槽口, 尺寸如下表

齿数	S	GD
9	6.4	29
10		34
11		39
12		44
13		49

交货期	小单	大单
	1-20	21-
	正常	报价

货期	DSFA10AB	DSFB10AB	DSFC10AB
	3天发货	7天发货	现询

G5
拉手/合页
手柄/手轮
门组件