


图材质: GCr15
图硬度: 58HRC~ 视角标准: 第一视角



D	槽数(个)				
	30~	40~	60~	70~	80~
8	2	3	4	5	-
10	2	3	4	5	6
13	2	3	4	5	6
16	2	3	4	5	6
20	2	3	4	5	6
25	2	3	4	5	6

图材质: GCr15
图硬度: 58HRC~ 视角标准: 第一视角



①代号 - ②D - ③L
GPAJYU - D10 - L40

M×I 螺距	D1	R	V	①型式②D	③L						
M5×12 P0.8	13	1	8	8	30	40	50	60	70		
	16				30	40	50	60	70	80	
M6×15 P1.0	20	1.5	10	13		40	50	60	70	80	
	23					40	50	60	70	80	90
M8×20 P1.25	27	2	13	20		50	60	70	80	90	100
	32					60	70	80	90	100	110
				25						110	120



<p>缩短</p>	LD	变更全长 指30≤LD<L 定单位0.5mm
<p>伸长</p>	LD	变更全长(长型LD) D LD 指定单位 0.5mm 8 70<LD≤80 10 80<LD≤100 13 100<LD≤120 16 120<LD≤140 20 120<LD≤140 25 120<LD≤140

	VD	变更V尺寸 指定单位1mm 5≤VD<V M螺纹深度缩短(V-VD)												
	GD	对导柱前端进行 锥度加工。 <table border="1"> <thead> <tr> <th>D</th> <th>F</th> </tr> </thead> <tbody> <tr><td>8</td><td rowspan="3">3</td></tr> <tr><td>10</td></tr> <tr><td>13</td></tr> <tr><td>16</td><td rowspan="3">5</td></tr> <tr><td>20</td></tr> <tr><td>25</td></tr> </tbody> </table>	D	F	8	3	10	13	16	5	20	25		
D	F													
8	3													
10														
13														
16	5													
20														
25														
	RD	变更前端R <table border="1"> <thead> <tr> <th>D</th> <th>标准R</th> <th>RD(选择)</th> </tr> </thead> <tbody> <tr> <td>8·10</td> <td>1.0</td> <td>1.5·2.0</td> </tr> <tr> <td>13·16</td> <td>1.5</td> <td>2.0·2.5</td> </tr> <tr> <td>20·25</td> <td>2.0</td> <td>2.5·3.0</td> </tr> </tbody> </table>	D	标准R	RD(选择)	8·10	1.0	1.5·2.0	13·16	1.5	2.0·2.5	20·25	2.0	2.5·3.0
D	标准R	RD(选择)												
8·10	1.0	1.5·2.0												
13·16	1.5	2.0·2.5												
20·25	2.0	2.5·3.0												



交货期 **3天发货**



数量分类	标准订单	特殊订单
数量	小单	大单
交货期	1~30	30~
	通常	另行报价

▲常州·东莞发货。
▲部分产品8天发货, 请以实际报价为准。

