

精制联轴器·十字滑块型


夹紧型



产品特点：主体采用 A2017 阳极氧化处理，容许误差可调整，轴向反作用力小，有良好的电绝缘性，用于阴极溅镀装置 / 零件送料器 / 缝纫机 / 娱乐器材。



① 代号	轴套 [M] 材质	弹性体 [M] 材质	[S] 表面处理
CGHAC	A2017	聚氨酯	阳极氧化处理



订购编号示例

① 代号	-	② D	-	③ L	-	④ c	-	⑤ d
CGHAC	-	12	-	16.5	-	c3	-	d4

① 代号	② D	③ L	④ c ⑤ d 可选范围																
CGHAC	12	16.5	3	4	5														
	15	18.8		4	5	6													
	17	24.5			5	6	6.35												
	20	27.4			5	6	6.35	8	9.525	10									
	26	30.4				6	6.35	8	9.525	10	12	14							
	30	32.5						8	9.525	10	12	14							
	34	34								10	12	14	15	16					
	38	40								10	12	14	15	16	18	20			
	45	46									12	14	15	16	18	20			
	55	57											16	18	20	22	25		
68	77													20	22	25	28	30	35

① 代号	② D	F	M	紧固螺钉扭 矩 (N·m)	额定扭矩 (N·m)	容许偏心 (mm)	容许偏角 (°)	容许转速 (rpm)	惯性矩 (kg·m ²)	重量 (g)
CGHAC	12	2.5	M2	0.5	1	1	3	52000	6.6x10 ⁻⁸	3
	15	2.9	M2.5	1	1.6	1	3	42000	1.7x10 ⁻⁷	5
	17	3.7	M2.5	1	2.2	1.2	3	37000	3.8x10 ⁻⁷	9
	20	4.4	M3	1.5	3.2	1.2	3	31000	8.0x10 ⁻⁷	13
	26	4.9	M3	1.5	6	1.5	3	24000	2.5x10 ⁻⁶	24
	30	5	M4	2.5	15	2	3	21000	5.3x10 ⁻⁶	39
	34	5.6	M4	2.5	16	2.5	3	18000	8.6x10 ⁻⁶	50
	38	6	M5	4	28	2.5	3	16000	1.5x10 ⁻⁵	67
	45	6.9	M5	4	30	3	3	14000	3.2x10 ⁻⁵	110
	55	9.4	M6	8	45	4	3	11000	1.0x10 ⁻⁴	230
68	12	M8	16	80	4.5	3	9000	3.3x10 ⁻⁴	440	

▲以上参数由最大孔径测得。