



★ 产品特点: 为自润滑型产品, 可减少涂抹的润滑脂量。




①代号	类型	线性滑板厚度	④材质
OFSL	两面研磨型	10mm	高力黄铜+ 固体润滑剂
OFSLUP		5mm	
OFSLU		5mm	
OFSLT		3mm	


OFSLT
(板厚3mm)




OFSLU
(板厚5mm)



OFSLUP
(板厚5mm)




OFSL
(板厚10mm)




1孔型




2孔型




3孔型



4孔型




5孔型




4孔型





6孔型



8孔型




10孔型



视角标准: 第一视角


■ OFSL



Z(沉头孔)

w	d	d ₁	t	附属螺栓规格
20	4.5	8	4	M4-20
30	5.5	9.5	5	M5-20
40	6.5	11	6	M6-20
50				
60	9	15	6	M8-20
80				


■ OFSLUP



Z(沉头孔)

w	d	d ₁	t	附属螺栓规格
20	4.5	8	3	M4-10


■ OFSLU



P(平头孔)

w	d	d ₁	t	附属螺栓规格
20	4.5	9.5	2.5	M4-20
30	5.5	11.1	2.8	M5-20
40	6.5	13.1	3.3	M6-20
50				
60	9	17.6	4.3	M8-20
80				

■ OFSLT



P(平头孔)

w	d	d ₁	t	附属螺栓规格
20	4.5	9.5	2.5	M4-20
30	5.5	11.1	2.8	M5-20
40				