


按图定制

①代号	边长	④材质	⑤表面处理	最高使用压力
MAHDGKT	25×25	铝合金	本色阳极氧化	1MPa(≈10.2Kgf/cm²)以下
MAHDGKU	35×35			

▲由于批次不同, 发货带表面处理产品可能存在色差, 不影响尺寸及功能。



①代号 - ②侧面孔数K - ③螺纹代号L  
MAHDGKT - K3 - L55

①代号	②侧面孔数K	③螺纹代号L	d Rc(PT)/M
	K	L	
MAHDGKT (25×25)	1	11	1/8
		55	M5
	2	11	1/8
		55	M5
	3	11	1/8
		55	M5
	4	11	1/8
		55	M5
	5	11	1/8
		55	M5
	6	11	1/8
		55	M5
MAHDGKU (35×35)	1	22N	1/4
	2		
	3		
	4		
	5		
	6		

▲螺纹代号: 如11, 表示d为1/8管螺纹。

螺纹尺寸	M5	R1/8	R1/4	R3/8	R1/2	R3/4
紧固扭矩 N·m (Kgf·cm)	0.5~1 (5~10)	4~6 (40~60)	7~9 (70~90)	10~13 (100~130)	20~23 (200~230)	30~35 (300~350)

▲推荐紧固扭矩(如果紧固时超过推荐的紧固扭矩, 则可能会导致螺纹部损坏, 造成外螺纹相互干扰。)



爱安特自营商城焕新登场, 注册有礼, 一键直达



400-6699-428



www.ant-fa.com