




★ 产品特点: 为自润滑型产品, 可减少涂抹的润滑脂量。


	1 代号 OFSPZ	类型 自由指定型	材质 高力黄铜+固体润滑剂
---	----------------------	-------------	------------------




2H(2孔)




2HA(2孔)




2HB(2孔)



3H(3孔)



4H(4孔)



6H(6孔)

视图标准: 第一视角



1 代号 -
 2 公称尺寸 -
 3 A(长) -
 4 B(宽) -
 5 T(厚度) -
 6 螺孔形式规格
 OFSPZ - 3H - A160 - B60 - T10 - P6

1 代号	2 公称尺寸	最小单位: mm		5 T(厚度)	6 螺孔形式规格		X	Y
		长: 3 A	宽: 4 B		T=5	T=10		
OFSPZ	2H	50-60	28-80	5	P5	P6	30	-
		61-80					40	
		81-100					60	
		101-120					80	
		121-150					100	
	3H	151-180	50-100	5	P5	P6	65x2	30(B≤80)
		181-200					80x2	
	2HA 2HB	50-60	50-100	5	P5	P6	30	30(B≤80)
		61-80					40	
		81-100					60	
		101-120					80	
	4H	80-100	50-100	5	P5	P6	60	30(B≤80)
101-120		80						
121-150		100						
6H	151-180	100-150	5	P6	P6	65x2	80(B≤120)	
	180-200					80x2		100(B≥121)

螺孔形式规格	M×L		
	P5	P6/Z6	Z8
T=5	M5×16	M6×16	-
T=10	-	M6×20	M8×20

螺孔形式规格	平头螺栓孔 P(平头孔)		沉头螺栓孔 Z(沉头孔)	
	P5	P6	Z6	Z8
d	5.3	6.5	6.5	8.5
d1	11.5	13.5	11	14
t	3	3.5	4.5	5.5

B2 无油衬套



交货期 5天发货



数量 1~9 10~
折扣率 100% 现询